

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760797

Luminaire Tested: LD6D10D010-EU6DR700210IC9024-6LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P760797  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D10D010-EU6DR700210IC9024-6LBSQW1MW  
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 752.8 lumens  
Efficiency: N/A  
Efficacy: 64.3 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P760797  
CATALOG NUMBER: LD6D10D010-EU6DR700210IC9024-6LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P760797

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9024-6LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	88	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	53	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	92500
5°	89750
10°	87248
15°	86103
20°	80403
25°	60399
30°	42694
35°	15126
40°	7944
45°	8468
50°	8771
55°	8934
60°	8981
65°	8790
70°	8306
75°	7683
80°	6795
85°	5516

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 8988 cd/sqm



TEST NUMBER: P760797

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9024-6LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.2	10.3
10°-20°	211.7	28.1
20°-30°	233.2	31.0
30°-40°	89.1	11.8
40°-50°	42.0	5.6
50°-60°	41.8	5.6
60°-70°	33.4	4.4
70°-80°	19.2	2.6
80°-90°	5.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	522.0	69.3
0°-40°	611.1	81.2
0°-60°	694.9	92.3
0°-90°	752.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	752.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	847	
5°	818	77
15°	761	212
25°	501	233
35°	113	89
45°	55	42
55°	47	42
65°	34	33
75°	18	19
85°	4	5
90°	0	



TEST NUMBER: P760797

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9024-6LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	846.6
2.5°	837.7
5°	818.3
7.5°	802.1
10°	786.4
12.5°	773.1
15°	761.2
17.5°	732.3
20°	691.5
22.5°	603.3
25°	501.0
27.5°	436.1
30°	338.4
32.5°	218.6
35°	113.4
37.5°	61.2
40°	55.7
42.5°	55.3
45°	54.8
47.5°	53.6
50°	51.6
52.5°	49.3
55°	46.9
57.5°	44.2
60°	41.1
62.5°	37.6
65°	34.0
67.5°	30.0
70°	26.0
72.5°	22.0
75°	18.2
77.5°	14.3
80°	10.8
82.5°	7.6
85°	4.4
87.5°	1.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)