

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760020

Luminaire Tested: LD6D10D010-EU6DR200210IC9027-6LBCSSQMW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P760020  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D10D010-EU6DR200210IC9027-6LBCSSQMW  
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 996.9 lumens  
Efficiency: N/A  
Efficacy: 85.2 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P760020  
CATALOG NUMBER: LD6D10D010-EU6DR200210IC9027-6LBCSSQMW

### Luminous Intensity Polar Plot





TEST NUMBER: P760020

CATALOG NUMBER: LD6D10D010-EU6DR200210IC9027-6LBCSSQMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	99	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	98	96	95																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	95	93	92																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	93	91	89																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	91	88	86																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	88	86	84																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	86	84	82																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	84	82	80																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	82	80	78																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	81	78	76																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	619946
5°	559304
10°	313911
15°	159571
20°	67555
25°	31188
30°	16515
35°	8897
40°	4750
45°	2812
50°	1632
55°	857
60°	546
65°	388
70°	160
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2812 cd/sqm



TEST NUMBER: P760020

CATALOG NUMBER: LD6D10D010-EU6DR200210IC9027-6LBCSSQMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	404.0	40.5
10°-20°	397.8	39.9
20°-30°	130.0	13.0
30°-40°	44.3	4.4
40°-50°	14.9	1.5
50°-60°	4.5	0.4
60°-70°	1.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	931.7	93.5
0°-40°	976.0	97.9
0°-60°	995.3	99.8
0°-90°	996.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	996.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5674	
5°	5100	404
15°	1411	398
25°	259	130
35°	67	44
45°	18	15
55°	4	4
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P760020

CATALOG NUMBER: LD6D10D010-EU6DR200210IC9027-6LBCSSQMW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5674.0
0.5°	5674.0
1°	5666.9
1.5°	5652.7
2°	5627.0
2.5°	5592.6
3°	5544.1
3.5°	5476.4
4°	5375.9
4.5°	5253.6
5°	5099.5
5.5°	4896.9
6°	4689.2
6.5°	4451.2
7°	4218.3
7.5°	3945.5
8°	3702.0
8.5°	3456.9
9°	3230.6
9.5°	3022.9
10°	2829.4
12.5°	2031.6
15°	1410.7
17.5°	921.6
20°	581.0
22.5°	376.4
25°	258.7
27.5°	181.9
30°	130.9
32.5°	94.0
35°	66.7
37.5°	46.5
40°	33.3
42.5°	24.3
45°	18.2
47.5°	14.1
50°	9.6
52.5°	6.1
55°	4.5
57.5°	3.5
60°	2.5
62.5°	2.0
65°	1.5



TEST NUMBER: P760020  
CATALOG NUMBER: LD6D10D010-EU6DR200210IC9027-6LBCSSQMW

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		1.0
70°		0.5

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)