

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760200

Luminaire Tested: LD6D10D010-EU6DR300210IC9035-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760200
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR300210IC9035-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 978.5 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760200

CATALOG NUMBER: LD6D10D010-EU6DR300210IC9035-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P760200

CATALOG NUMBER: LD6D10D010-EU6DR300210IC9035-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96								
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92								
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89								
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85								
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82								
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79								
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77								
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74								
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72								
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	240813	240813	240813
5°	233903	233627	233919
10°	202596	201166	202549
15°	132186	131473	130815
20°	65727	68195	65645
25°	33107	37338	32431
30°	13258	14442	11552
35°	6148	5887	4934
40°	2658	2948	2498
45°	1873	2327	1894
50°	643	1691	679
55°	374	707	387
60°	260	306	260
65°	163	163	163
70°	112	67	112
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 2327 cd/sqm



TEST NUMBER: P760200

CATALOG NUMBER: LD6D10D010-EU6DR300210IC9035-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.7	28.3
10°-20°	445.6	45.5
20°-30°	192.5	19.7
30°-40°	43.9	4.5
40°-50°	15.1	1.5
50°-60°	3.7	0.4
60°-70°	1.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	914.8	93.5
0°-40°	958.6	98.0
0°-60°	977.4	99.9
0°-90°	978.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	978.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3146	3146	3146	3146	3146	
5°	3044	3041	3041	3047	3044	277
15°	1668	1648	1659	1654	1651	447
25°	392	407	442	396	384	188
35°	66	67	63	63	53	45
45°	17	22	22	22	18	12
55°	3	3	5	3	3	3
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P760200

CATALOG NUMBER: LD6D10D010-EU6DR300210IC9035-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3146.1	3146.1	3146.1	3146.1	3146.1
2.5°	3125.3	3123.2	3124.4	3125.9	3126.5
5°	3044.2	3041.3	3040.6	3047.0	3044.4
7.5°	2880.6	2876.4	2870.1	2884.5	2897.9
10°	2606.6	2601.9	2588.2	2595.0	2606.0
12.5°	2202.1	2187.1	2186.8	2208.4	2205.5
15°	1668.1	1648.0	1659.1	1653.7	1650.8
17.5°	1121.7	1114.0	1128.8	1124.4	1105.1
20°	806.9	808.9	837.2	823.0	805.9
22.5°	588.8	596.1	629.6	593.0	579.5
25°	392.0	406.9	442.1	396.5	384.0
27.5°	241.1	247.9	283.6	238.0	231.2
30°	150.0	146.6	163.4	140.3	130.7
32.5°	98.4	94.1	99.5	89.3	81.5
35°	65.8	67.2	63.0	62.6	52.8
37.5°	41.1	47.3	41.7	44.5	34.0
40°	26.6	34.3	29.5	32.6	25.0
42.5°	21.8	26.4	24.2	25.8	22.2
45°	17.3	21.5	21.5	21.5	17.5
47.5°	9.6	14.4	18.4	14.7	10.2
50°	5.4	7.3	14.2	7.6	5.7
52.5°	3.7	4.2	9.7	4.3	3.8
55°	2.8	2.9	5.3	3.1	2.9
57.5°	2.2	2.3	2.8	2.3	2.2
60°	1.7	1.7	2.0	1.8	1.7
62.5°	1.3	1.3	1.4	1.3	1.3
65°	0.9	0.9	0.9	0.9	0.9
67.5°	0.5	0.6	0.6	0.6	0.6
70°	0.5	0.3	0.3	0.3	0.5
72.5°	0.3	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)