

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760058

Luminaire Tested: LD6D10D010-EU6DR200210IC9040-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760058
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR200210IC9040-6LBCSSQMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1116.7 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760058

CATALOG NUMBER: LD6D10D010-EU6DR200210IC9040-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P760058

CATALOG NUMBER: LD6D10D010-EU6DR200210IC9040-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	97	94															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	91															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	93	88															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	93	89	85															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	91	88	83															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	88	86	81															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	86	84	79															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	84	82	77															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	82	80	77															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	81	78	75															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	694450
5°	626525
10°	351644
15°	178744
20°	75682
25°	34937
30°	18496
35°	9964
40°	5334
45°	3152
50°	1836
55°	972
60°	612
65°	440
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3152 cd/sqm



TEST NUMBER: P760058

CATALOG NUMBER: LD6D10D010-EU6DR200210IC9040-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	452.5	40.5
10°-20°	445.6	39.9
20°-30°	145.6	13.0
30°-40°	49.6	4.4
40°-50°	16.7	1.5
50°-60°	5.0	0.5
60°-70°	1.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1043.7	93.5
0°-40°	1093.3	97.9
0°-60°	1115.0	99.8
0°-90°	1116.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1116.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6356	
5°	5712	453
15°	1580	446
25°	290	146
35°	75	50
45°	20	17
55°	5	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P760058

CATALOG NUMBER: LD6D10D010-EU6DR200210IC9040-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	6355.9
0.5°	6355.9
1°	6348.0
1.5°	6332.1
2°	6303.2
2.5°	6264.8
3°	6210.4
3.5°	6134.6
4°	6022.0
4.5°	5885.0
5°	5712.4
5.5°	5485.4
6°	5252.8
6.5°	4986.2
7°	4725.3
7.5°	4419.7
8°	4146.9
8.5°	3872.4
9°	3618.8
9.5°	3386.2
10°	3169.5
12.5°	2275.8
15°	1580.2
17.5°	1032.3
20°	650.9
22.5°	421.7
25°	289.8
27.5°	203.8
30°	146.6
32.5°	105.3
35°	74.7
37.5°	52.1
40°	37.4
42.5°	27.2
45°	20.4
47.5°	15.8
50°	10.8
52.5°	6.8
55°	5.1
57.5°	4.0
60°	2.8
62.5°	2.3
65°	1.7



TEST NUMBER: P760058
CATALOG NUMBER: LD6D10D010-EU6DR200210IC9040-6LBCSSQMMS

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.1
70°		0.6

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)