

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757819

Luminaire Tested: LD6D02D010-EU6DR700210IC9050-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P757819
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR700210IC9050-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 242.2 lumens
Efficiency: N/A
Efficacy: 47.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757819

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9050-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P757819

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9050-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	88	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	53	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29763
5°	28878
10°	28069
15°	27702
20°	25871
25°	19434
30°	13739
35°	4868
40°	2553
45°	2720
50°	2822
55°	2876
60°	2884
65°	2818
70°	2683
75°	2448
80°	2202
85°	1755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 2888 cd/sqm



TEST NUMBER: P757819

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9050-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.8	10.3
10°-20°	68.1	28.1
20°-30°	75.0	31.0
30°-40°	28.7	11.8
40°-50°	13.5	5.6
50°-60°	13.5	5.6
60°-70°	10.8	4.4
70°-80°	6.2	2.5
80°-90°	1.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	168.0	69.3
0°-40°	196.6	81.2
0°-60°	223.6	92.3
0°-90°	242.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	242.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	272	
5°	263	25
15°	245	68
25°	161	75
35°	36	29
45°	18	14
55°	15	13
65°	11	11
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P757819

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9050-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	272.4
2.5°	269.6
5°	263.3
7.5°	258.1
10°	253.0
12.5°	248.8
15°	244.9
17.5°	235.7
20°	222.5
22.5°	194.1
25°	161.2
27.5°	140.3
30°	108.9
32.5°	70.4
35°	36.5
37.5°	19.7
40°	17.9
42.5°	17.8
45°	17.6
47.5°	17.2
50°	16.6
52.5°	15.9
55°	15.1
57.5°	14.2
60°	13.2
62.5°	12.1
65°	10.9
67.5°	9.7
70°	8.4
72.5°	7.0
75°	5.8
77.5°	4.6
80°	3.5
82.5°	2.5
85°	1.4
87.5°	0.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)