

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760692

Luminaire Tested: LD6D10D010-EU6DR600210IC9040-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P760692
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR600210IC9040-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 902.3 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760692
CATALOG NUMBER: LD6D10D010-EU6DR600210IC9040-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P760692

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9040-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	117084
5°	119966
10°	121409
15°	115660
20°	101983
25°	82484
30°	55789
35°	27957
40°	4536
45°	4435
50°	4521
55°	4591
60°	4720
65°	4835
70°	4952
75°	5024
80°	4845
85°	4012

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 5024 cd/sqm



TEST NUMBER: P760692

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9040-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.5	11.6
10°-20°	282.8	31.3
20°-30°	304.3	33.7
30°-40°	132.3	14.7
40°-50°	22.2	2.5
50°-60°	21.6	2.4
60°-70°	18.5	2.0
70°-80°	12.4	1.4
80°-90°	3.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	691.7	76.7
0°-40°	823.9	91.3
0°-60°	867.7	96.2
0°-90°	902.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	902.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1072	
5°	1094	105
15°	1022	283
25°	684	304
35°	210	132
45°	29	22
55°	24	22
65°	19	18
75°	12	12
85°	3	4
90°	0	



TEST NUMBER: P760692
CATALOG NUMBER: LD6D10D010-EU6DR600210IC9040-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1071.6
2.5°	1101.7
5°	1093.8
7.5°	1096.3
10°	1094.3
12.5°	1071.7
15°	1022.5
17.5°	956.4
20°	877.1
22.5°	792.1
25°	684.2
27.5°	547.2
30°	442.2
32.5°	340.8
35°	209.6
37.5°	89.7
40°	31.8
42.5°	29.3
45°	28.7
47.5°	27.7
50°	26.6
52.5°	25.4
55°	24.1
57.5°	22.9
60°	21.6
62.5°	20.2
65°	18.7
67.5°	17.1
70°	15.5
72.5°	13.7
75°	11.9
77.5°	9.7
80°	7.7
82.5°	5.4
85°	3.2
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)