

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760003

Luminaire Tested: LD6D10D010-EU6DR150210IC9050-6LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760003
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR150210IC9050-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 972.6 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760003
CATALOG NUMBER: LD6D10D010-EU6DR150210IC9050-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P760003

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9050-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1491126	1491126	1491126
5°	876255	864913	871752
10°	261523	263351	267382
15°	65047	66315	64274
20°	19466	22542	19875
25°	6863	8740	6949
30°	2523	3317	2561
35°	1264	1423	1220
40°	795	873	795
45°	588	630	588
50°	466	466	466
55°	390	390	390
60°	316	316	316
65°	243	243	243
70°	205	205	205
75°	128	128	166
80°	87	87	87
85°	50	50	50

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 630 cd/sqm



TEST NUMBER: P760003

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9050-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	630.8	64.9
10°-20°	259.5	26.7
20°-30°	51.5	5.3
30°-40°	12.9	1.3
40°-50°	6.8	0.7
50°-60°	5.0	0.5
60°-70°	3.6	0.4
70°-80°	2.0	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	941.8	96.8
0°-40°	954.7	98.2
0°-60°	966.5	99.4
0°-90°	972.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	972.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	13252	13252	13252	13252	13252	
5°	8622	8534	8510	8569	8578	630
15°	749	763	764	750	740	257
25°	88	100	112	99	89	46
35°	17	18	20	18	17	12
45°	8	8	9	8	8	7
55°	6	6	6	6	6	5
65°	3	3	3	3	3	4
75°	2	2	2	2	2	2
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P760003

CATALOG NUMBER: LD6D10D010-EU6DR150210IC9050-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	13252.1	13252.1	13252.1	13252.1	13252.1
2.5°	11954.0	11964.1	11968.0	11979.8	12023.5
5°	8622.1	8533.5	8510.5	8569.4	8577.8
7.5°	5107.4	5125.4	5191.0	5205.6	5152.9
10°	2802.8	2825.8	2822.4	2842.6	2865.6
12.5°	1433.4	1415.4	1409.8	1432.8	1400.8
15°	748.9	763.0	763.5	750.1	740.0
17.5°	402.8	419.1	446.0	424.1	390.5
20°	237.9	252.5	275.5	257.5	242.9
22.5°	147.0	158.8	175.0	161.0	149.2
25°	88.1	99.9	112.2	99.3	89.2
27.5°	52.2	62.3	70.1	61.7	51.6
30°	33.7	39.3	44.3	38.7	34.2
32.5°	23.6	25.8	28.1	25.8	23.6
35°	17.4	18.5	19.6	18.5	16.8
37.5°	13.5	14.6	15.1	14.0	12.9
40°	11.2	11.8	12.3	11.8	11.2
42.5°	9.5	10.1	10.1	10.1	9.5
45°	8.4	8.4	9.0	8.4	8.4
47.5°	7.3	7.3	7.9	7.3	7.3
50°	6.7	6.7	6.7	6.7	6.7
52.5°	6.2	6.2	6.2	6.2	6.2
55°	5.6	5.6	5.6	5.6	5.6
57.5°	5.0	5.0	5.0	5.0	5.0
60°	4.5	4.5	4.5	4.5	4.5
62.5°	3.9	3.9	3.9	3.9	3.9
65°	3.4	3.4	3.4	3.4	3.4
67.5°	3.4	3.4	3.4	3.4	3.4
70°	2.8	2.8	2.8	2.8	2.8
72.5°	2.2	2.2	2.2	2.2	2.2
75°	1.7	1.7	1.7	1.7	2.2
77.5°	1.7	1.7	1.7	1.7	1.7
80°	1.1	1.1	1.1	1.1	1.1
82.5°	1.1	1.1	1.1	1.1	1.1
85°	0.6	0.6	0.6	0.6	0.6
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)