

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760950

Luminaire Tested: LD6D15D010-EU6DR1515309024-6LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR1515309024-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1063.6 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760950

CATALOG NUMBER: LD6D15D010-EU6DR1515309024-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P760950

CATALOG NUMBER: LD6D15D010-EU6DR1515309024-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98					98			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96					96			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94					94			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93					93			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92					92			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90					90			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89					89			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88					88			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87					87			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86					86			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1630538	1630538	1630538
5°	958188	945779	953259
10°	285969	287975	292389
15°	71136	72517	70285
20°	21282	24645	21732
25°	7502	9558	7595
30°	2756	3632	2801
35°	1380	1561	1336
40°	873	959	873
45°	644	686	644
50°	515	515	515
55°	425	425	425
60°	344	344	344
65°	264	264	264
70°	227	227	227
75°	136	136	189
80°	95	95	95
85°	50	50	50

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 686 cd/sqm



TEST NUMBER: P760950

CATALOG NUMBER: LD6D15D010-EU6DR1515309024-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	689.8	64.9
10°-20°	283.7	26.7
20°-30°	56.4	5.3
30°-40°	14.1	1.3
40°-50°	7.4	0.7
50°-60°	5.5	0.5
60°-70°	3.9	0.4
70°-80°	2.2	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1029.9	96.8
0°-40°	1044.0	98.2
0°-60°	1056.8	99.4
0°-90°	1063.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1063.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	14491	14491	14491	14491	14491	
5°	9428	9331	9306	9371	9380	689
15°	819	834	835	820	809	281
25°	96	109	123	109	98	51
35°	19	20	22	20	18	13
45°	9	9	10	9	9	7
55°	6	6	6	6	6	5
65°	4	4	4	4	4	4
75°	2	2	2	2	2	2
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P760950

CATALOG NUMBER: LD6D15D010-EU6DR1515309024-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	14491.1	14491.1	14491.1	14491.1	14491.1
2.5°	13071.6	13082.6	13086.9	13099.8	13147.7
5°	9428.3	9331.3	9306.2	9370.6	9379.8
7.5°	5584.9	5604.6	5676.3	5692.3	5634.6
10°	3064.8	3090.0	3086.3	3108.4	3133.6
12.5°	1567.4	1547.8	1541.6	1566.8	1531.8
15°	819.0	834.3	834.9	820.2	809.2
17.5°	440.5	458.3	487.7	463.8	427.0
20°	260.1	276.1	301.2	281.6	265.6
22.5°	160.7	173.6	191.4	176.1	163.2
25°	96.3	109.2	122.7	108.6	97.5
27.5°	57.1	68.1	76.7	67.5	56.4
30°	36.8	42.9	48.5	42.3	37.4
32.5°	25.8	28.2	30.7	28.2	25.8
35°	19.0	20.2	21.5	20.2	18.4
37.5°	14.7	15.9	16.6	15.3	14.1
40°	12.3	12.9	13.5	12.9	12.3
42.5°	10.4	11.0	11.0	11.0	10.4
45°	9.2	9.2	9.8	9.2	9.2
47.5°	8.0	8.0	8.6	8.0	8.0
50°	7.4	7.4	7.4	7.4	7.4
52.5°	6.7	6.7	6.7	6.7	6.7
55°	6.1	6.1	6.1	6.1	6.1
57.5°	5.5	5.5	5.5	5.5	5.5
60°	4.9	4.9	4.9	4.9	4.9
62.5°	4.3	4.3	4.3	4.3	4.3
65°	3.7	3.7	3.7	3.7	3.7
67.5°	3.7	3.7	3.7	3.7	3.7
70°	3.1	3.1	3.1	3.1	3.1
72.5°	2.5	2.5	2.5	2.5	2.5
75°	1.8	1.8	1.8	1.8	2.5
77.5°	1.8	1.8	1.8	1.8	1.8
80°	1.2	1.2	1.2	1.2	1.2
82.5°	1.2	1.2	1.2	1.2	1.2
85°	0.6	0.6	0.6	0.6	0.6
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)