

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763677

Luminaire Tested: LD6D25D010-EU6DR6520359030-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P763677
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR6520359030-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2235.2 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763677

CATALOG NUMBER: LD6D25D010-EU6DR6520359030-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P763677

CATALOG NUMBER: LD6D25D010-EU6DR6520359030-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	240461
5°	240656
10°	249130
15°	249543
20°	229744
25°	195747
30°	149857
35°	105879
40°	62486
45°	25372
50°	9196
55°	5124
60°	2950
65°	1603
70°	1693
75°	1351
80°	1384
85°	1128

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25372 cd/sqm



TEST NUMBER: P763677

CATALOG NUMBER: LD6D25D010-EU6DR6520359030-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.9	9.5
10°-20°	611.3	27.3
20°-30°	733.4	32.8
30°-40°	492.9	22.1
40°-50°	147.5	6.6
50°-60°	26.0	1.2
60°-70°	7.4	0.3
70°-80°	3.7	0.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1556.6	69.6
0°-40°	2049.5	91.7
0°-60°	2223.1	99.5
0°-90°	2235.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2235.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2201	
5°	2194	212
15°	2206	611
25°	1624	733
35°	794	493
45°	164	148
55°	27	26
65°	6	7
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P763677

CATALOG NUMBER: LD6D25D010-EU6DR6520359030-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2200.8
2.5°	2210.2
5°	2194.2
7.5°	2227.3
10°	2245.5
12.5°	2241.1
15°	2206.1
17.5°	2120.4
20°	1975.9
22.5°	1805.8
25°	1623.7
27.5°	1418.3
30°	1187.8
32.5°	978.9
35°	793.8
37.5°	610.8
40°	438.1
42.5°	286.1
45°	164.2
47.5°	86.9
50°	54.1
52.5°	37.5
55°	26.9
57.5°	19.4
60°	13.5
62.5°	8.8
65°	6.2
67.5°	5.6
70°	5.3
72.5°	4.1
75°	3.2
77.5°	2.8
80°	2.2
82.5°	1.5
85°	0.9
87.5°	0.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)