

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761783

Luminaire Tested: LD6D15D010-EU6DR700215IC9024-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P761783
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR700215IC9024-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1011.8 lumens
Efficiency: N/A
Efficacy: 64.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761783
CATALOG NUMBER: LD6D15D010-EU6DR700215IC9024-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P761783

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9024-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	124284
5°	120591
10°	117237
15°	115694
20°	108041
25°	81158
30°	57379
35°	20314
40°	10683
45°	11388
50°	11780
55°	12001
60°	12084
65°	11815
70°	11149
75°	10343
80°	9186
85°	7522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 12084 cd/sqm



TEST NUMBER: P761783

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9024-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.7	10.3
10°-20°	284.5	28.1
20°-30°	313.3	31.0
30°-40°	119.7	11.8
40°-50°	56.5	5.6
50°-60°	56.2	5.6
60°-70°	45.0	4.4
70°-80°	25.9	2.6
80°-90°	7.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	701.5	69.3
0°-40°	821.2	81.2
0°-60°	933.9	92.3
0°-90°	1011.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1011.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1138	
5°	1100	104
15°	1023	284
25°	673	313
35°	152	120
45°	74	57
55°	63	56
65°	46	45
75°	24	26
85°	6	7
90°	0	



TEST NUMBER: P761783

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9024-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1137.5
2.5°	1125.7
5°	1099.5
7.5°	1077.8
10°	1056.7
12.5°	1038.9
15°	1022.8
17.5°	984.1
20°	929.2
22.5°	810.7
25°	673.2
27.5°	586.1
30°	454.8
32.5°	293.8
35°	152.3
37.5°	82.3
40°	74.9
42.5°	74.4
45°	73.7
47.5°	72.0
50°	69.3
52.5°	66.3
55°	63.0
57.5°	59.4
60°	55.3
62.5°	50.6
65°	45.7
67.5°	40.3
70°	34.9
72.5°	29.6
75°	24.5
77.5°	19.3
80°	14.6
82.5°	10.3
85°	6.0
87.5°	2.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)