

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763133

Luminaire Tested: LD6D25D010-EU6DR3020359035-6LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P763133  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D25D010-EU6DR3020359035-6LBCSSQMMS  
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2669.4 lumens  
Efficiency: N/A  
Efficacy: 106.4 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P763133

CATALOG NUMBER: LD6D25D010-EU6DR3020359035-6LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P763133

CATALOG NUMBER: LD6D25D010-EU6DR3020359035-6LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	657003	657003	657003
5°	638137	637391	638175
10°	552728	548826	552596
15°	360622	358688	356889
20°	179317	186053	179081
25°	90326	101863	88476
30°	36167	39411	31509
35°	16773	16063	13465
40°	7244	8044	6825
45°	5109	6343	5153
50°	1750	4620	1858
55°	1014	1908	1068
60°	704	842	704
65°	453	453	453
70°	291	201	291
75°	0	118	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 6343 cd/sqm



TEST NUMBER: P763133

CATALOG NUMBER: LD6D25D010-EU6DR3020359035-6LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	754.8	28.3
10°-20°	1215.6	45.5
20°-30°	525.3	19.7
30°-40°	119.7	4.5
40°-50°	41.1	1.5
50°-60°	10.0	0.4
60°-70°	2.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2495.6	93.5
0°-40°	2615.4	98.0
0°-60°	2666.5	99.9
0°-90°	2669.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2669.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	8583	8583	8583	8583	8583	
5°	8305	8297	8296	8313	8306	755
15°	4551	4496	4526	4512	4504	1219
25°	1070	1110	1206	1082	1048	512
35°	180	183	172	171	144	122
45°	47	59	59	59	48	33
55°	8	8	14	8	8	7
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P763133

CATALOG NUMBER: LD6D25D010-EU6DR3020359035-6LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	8583.4	8583.4	8583.4	8583.4	8583.4
2.5°	8526.5	8520.6	8524.0	8528.1	8529.9
5°	8305.2	8297.2	8295.5	8312.8	8305.7
7.5°	7858.9	7847.6	7830.3	7869.5	7906.1
10°	7111.4	7098.7	7061.2	7079.8	7109.7
12.5°	6007.7	5966.8	5966.0	6025.0	6017.0
15°	4550.8	4496.1	4526.4	4511.6	4503.7
17.5°	3060.3	3039.2	3079.7	3067.5	3014.8
20°	2201.4	2206.9	2284.1	2245.3	2198.5
22.5°	1606.4	1626.3	1717.7	1617.8	1581.2
25°	1069.5	1110.0	1206.1	1081.8	1047.6
27.5°	657.8	676.4	773.7	649.4	630.9
30°	409.2	399.9	445.9	382.6	356.5
32.5°	268.4	256.6	271.4	243.6	222.5
35°	179.5	183.3	171.9	170.7	144.1
37.5°	112.1	129.0	113.8	121.4	92.7
40°	72.5	93.6	80.5	88.9	68.3
42.5°	59.4	72.1	66.2	70.4	60.7
45°	47.2	58.6	58.6	58.6	47.6
47.5°	26.1	39.2	50.1	40.0	27.8
50°	14.7	19.8	38.8	20.6	15.6
52.5°	10.1	11.4	26.5	11.8	10.5
55°	7.6	8.0	14.3	8.4	8.0
57.5°	5.9	6.3	7.6	6.3	5.9
60°	4.6	4.6	5.5	5.0	4.6
62.5°	3.4	3.4	3.8	3.4	3.4
65°	2.5	2.5	2.5	2.5	2.5
67.5°	1.3	1.7	1.7	1.7	1.7
70°	1.3	0.9	0.9	0.9	1.3
72.5°	0.9	0.4	0.4	0.4	0.4
75°	0.0	0.0	0.4	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)