

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761181

Luminaire Tested: LD6D15D010-EU6DR300215IC9027-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761181
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR300215IC9027-6LBCSSQMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1206.1 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761181
CATALOG NUMBER: LD6D15D010-EU6DR300215IC9027-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P761181

CATALOG NUMBER: LD6D15D010-EU6DR300215IC9027-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	296858	296858	296858
5°	288342	287996	288349
10°	249743	247979	249681
15°	162949	162069	161253
20°	81024	84071	80918
25°	40818	46020	39982
30°	16342	17801	14239
35°	7578	7260	6083
40°	3277	3637	3078
45°	2306	2869	2327
50°	786	2084	834
55°	454	867	480
60°	321	383	321
65°	199	199	199
70°	134	90	134
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 2869 cd/sqm



TEST NUMBER: P761181

CATALOG NUMBER: LD6D15D010-EU6DR300215IC9027-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	341.0	28.3
10°-20°	549.2	45.5
20°-30°	237.3	19.7
30°-40°	54.1	4.5
40°-50°	18.6	1.5
50°-60°	4.5	0.4
60°-70°	1.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1127.6	93.5
0°-40°	1181.7	98.0
0°-60°	1204.8	99.9
0°-90°	1206.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1206.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3878	3878	3878	3878	3878	
5°	3753	3749	3748	3756	3753	341
15°	2056	2032	2045	2039	2035	551
25°	483	502	545	489	473	231
35°	81	83	78	77	65	55
45°	21	26	26	26	22	15
55°	3	4	6	4	4	3
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P761181

CATALOG NUMBER: LD6D15D010-EU6DR300215IC9027-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3878.3	3878.3	3878.3	3878.3	3878.3
2.5°	3852.6	3849.9	3851.4	3853.4	3854.1
5°	3752.7	3749.0	3748.2	3756.0	3752.8
7.5°	3551.0	3545.8	3538.0	3555.7	3572.3
10°	3213.2	3207.5	3190.5	3198.9	3212.4
12.5°	2714.5	2696.0	2695.7	2722.3	2718.7
15°	2056.3	2031.5	2045.2	2038.6	2034.9
17.5°	1382.8	1373.2	1391.5	1386.0	1362.2
20°	994.7	997.2	1032.1	1014.5	993.4
22.5°	725.9	734.8	776.1	731.0	714.4
25°	483.3	501.6	544.9	488.8	473.4
27.5°	297.2	305.6	349.6	293.4	285.0
30°	184.9	180.7	201.4	172.9	161.1
32.5°	121.3	116.0	122.6	110.1	100.6
35°	81.1	82.8	77.7	77.1	65.1
37.5°	50.6	58.3	51.4	54.8	41.9
40°	32.8	42.3	36.4	40.2	30.8
42.5°	26.9	32.5	29.9	31.8	27.4
45°	21.3	26.5	26.5	26.5	21.5
47.5°	11.8	17.7	22.6	18.1	12.5
50°	6.6	8.9	17.5	9.3	7.0
52.5°	4.6	5.2	12.0	5.3	4.8
55°	3.4	3.6	6.5	3.8	3.6
57.5°	2.7	2.9	3.4	2.9	2.7
60°	2.1	2.1	2.5	2.3	2.1
62.5°	1.5	1.5	1.7	1.5	1.5
65°	1.1	1.1	1.1	1.1	1.1
67.5°	0.6	0.7	0.7	0.7	0.7
70°	0.6	0.4	0.4	0.4	0.6
72.5°	0.4	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)