

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763756

Luminaire Tested: LD6D25D010-EU6DR7020359035-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P763756
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR7020359035-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2971.9 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763756
CATALOG NUMBER: LD6D25D010-EU6DR7020359035-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P763756
 CATALOG NUMBER: LD6D25D010-EU6DR7020359035-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71				
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60				
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56				
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51				
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48				
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	256293
5°	255649
10°	255099
15°	255029
20°	252533
25°	237218
30°	211488
35°	168622
40°	111964
45°	66937
50°	34693
55°	18230
60°	6446
65°	103
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 66937 cd/sqm



TEST NUMBER: P763756

CATALOG NUMBER: LD6D25D010-EU6DR7020359035-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.7	7.5
10°-20°	635.8	21.4
20°-30°	896.9	30.2
30°-40°	774.2	26.1
40°-50°	346.7	11.7
50°-60°	90.8	3.1
60°-70°	5.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1754.3	59.0
0°-40°	2528.5	85.1
0°-60°	2966.0	99.8
0°-90°	2971.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2971.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2346	
5°	2331	222
15°	2255	636
25°	1968	897
35°	1264	774
45°	433	347
55°	96	91
65°	0	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P763756
CATALOG NUMBER: LD6D25D010-EU6DR7020359035-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2345.7
2.5°	2343.1
5°	2330.9
7.5°	2320.8
10°	2299.3
12.5°	2279.9
15°	2254.6
17.5°	2225.5
20°	2171.9
22.5°	2083.8
25°	1967.7
27.5°	1833.2
30°	1676.3
32.5°	1484.3
35°	1264.2
37.5°	1021.2
40°	785.0
42.5°	596.4
45°	433.2
47.5°	298.6
50°	204.1
52.5°	140.9
55°	95.7
57.5°	57.8
60°	29.5
62.5°	9.3
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)