

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762990

Luminaire Tested: LD6D25D010-EU6DR2015309040-6LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P762990  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D25D010-EU6DR2015309040-6LBCSSQMMS  
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3046.5 lumens  
Efficiency: N/A  
Efficacy: 121.4 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P762990  
CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P762990

CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	96	95	94	94	93	92	91	91																			
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	93	92	91	91	90	89	88	88																			
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	90	89	88	87	86	85	85	84																			
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	87	86	85	84	83	82	81	81	80																			
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	84	83	82	81	80	79	78	77	77																			
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	82	81	80	79	78	77	76	75	75																			
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	80	79	78	77	76	75	74	73	73																			
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77	76	75	74	73	72	71	71																			
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	76	75	74	73	72	71	70	69	69																			
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	74	73	72	71	70	69	68	67	67																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1894603
5°	1709290
10°	959352
15°	487650
20°	206466
25°	95311
30°	50453
35°	27183
40°	14534
45°	8591
50°	4980
55°	2648
60°	1683
65°	1189
70°	479
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8591 cd/sqm



TEST NUMBER: P762990

CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1234.6	40.5
10°-20°	1215.7	39.9
20°-30°	397.2	13.0
30°-40°	135.2	4.4
40°-50°	45.5	1.5
50°-60°	13.7	0.4
60°-70°	4.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2847.4	93.5
0°-40°	2982.6	97.9
0°-60°	3041.8	99.8
0°-90°	3046.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3046.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	17340	
5°	15585	###
15°	4311	1216
25°	791	397
35°	204	135
45°	56	45
55°	14	14
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P762990

CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	17340.2
0.5°	17340.2
1°	17318.6
1.5°	17275.4
2°	17196.6
2.5°	17091.6
3°	16943.4
3.5°	16736.5
4°	16429.2
4.5°	16055.5
5°	15584.6
5.5°	14965.4
6°	14330.8
6.5°	13603.5
7°	12891.7
7.5°	12057.9
8°	11313.6
8.5°	10564.7
9°	9873.0
9.5°	9238.3
10°	8647.0
12.5°	6208.8
15°	4311.1
17.5°	2816.4
20°	1775.7
22.5°	1150.4
25°	790.6
27.5°	555.9
30°	399.9
32.5°	287.2
35°	203.8
37.5°	142.1
40°	101.9
42.5°	74.1
45°	55.6
47.5°	43.2
50°	29.3
52.5°	18.5
55°	13.9
57.5°	10.8
60°	7.7
62.5°	6.2
65°	4.6



TEST NUMBER: P762990  
CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBCSSQMMS

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





67.5°		3.1
70°		1.5

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)