

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761721

Luminaire Tested: LD6D15D010-EU6DR650215IC9027-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P761721
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9027-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 906.9 lumens
Efficiency: N/A
Efficacy: 57.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761721

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9027-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P761721

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9027-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97559
5°	97646
10°	101083
15°	101249
20°	93216
25°	79422
30°	60798
35°	42963
40°	25360
45°	10291
50°	3723
55°	2076
60°	1180
65°	646
70°	703
75°	549
80°	566
85°	501

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10291 cd/sqm



TEST NUMBER: P761721

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9027-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.0	9.5
10°-20°	248.0	27.3
20°-30°	297.6	32.8
30°-40°	200.0	22.1
40°-50°	59.9	6.6
50°-60°	10.5	1.2
60°-70°	3.0	0.3
70°-80°	1.5	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	631.6	69.6
0°-40°	831.6	91.7
0°-60°	902.0	99.5
0°-90°	906.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	906.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	893	
5°	890	86
15°	895	248
25°	659	298
35°	322	200
45°	67	60
55°	11	11
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P761721

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9027-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	892.9
2.5°	896.7
5°	890.3
7.5°	903.7
10°	911.1
12.5°	909.3
15°	895.1
17.5°	860.3
20°	801.7
22.5°	732.7
25°	658.8
27.5°	575.5
30°	481.9
32.5°	397.2
35°	322.1
37.5°	247.8
40°	177.8
42.5°	116.1
45°	66.6
47.5°	35.3
50°	21.9
52.5°	15.2
55°	10.9
57.5°	7.8
60°	5.4
62.5°	3.6
65°	2.5
67.5°	2.3
70°	2.2
72.5°	1.7
75°	1.3
77.5°	1.1
80°	0.9
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)