

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761052

Luminaire Tested: LD6D15D010-EU6DR2015309030-6LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761052
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR2015309030-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1182.9 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761052

CATALOG NUMBER: LD6D15D010-EU6DR2015309030-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P761052

CATALOG NUMBER: LD6D15D010-EU6DR2015309030-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91	88	86	85
6	99	93	89	86	98	92	88	86	91	87	85		90	87	84		88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82		87	84	82		86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78		83	80	78		82	80	78	77
10	89	83	79	76	88	82	79	76	82	78	76		81	78	76		81	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	735631
5°	663673
10°	372491
15°	189343
20°	80170
25°	37011
30°	19593
35°	10551
40°	5648
45°	3338
50°	1938
55°	1029
60°	656
65°	465
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3338 cd/sqm



TEST NUMBER: P761052

CATALOG NUMBER: LD6D15D010-EU6DR2015309030-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	479.4	40.5
10°-20°	472.0	39.9
20°-30°	154.2	13.0
30°-40°	52.5	4.4
40°-50°	17.7	1.5
50°-60°	5.3	0.4
60°-70°	1.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1105.6	93.5
0°-40°	1158.1	97.9
0°-60°	1181.1	99.8
0°-90°	1182.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1182.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6733	
5°	6051	479
15°	1674	472
25°	307	154
35°	79	53
45°	22	18
55°	5	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761052

CATALOG NUMBER: LD6D15D010-EU6DR2015309030-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	6732.8
0.5°	6732.8
1°	6724.4
1.5°	6707.6
2°	6677.0
2.5°	6636.3
3°	6578.7
3.5°	6498.4
4°	6379.1
4.5°	6234.0
5°	6051.1
5.5°	5810.7
6°	5564.3
6.5°	5281.9
7°	5005.5
7.5°	4681.8
8°	4392.8
8.5°	4102.0
9°	3833.4
9.5°	3587.0
10°	3357.4
12.5°	2410.7
15°	1673.9
17.5°	1093.6
20°	689.5
22.5°	446.7
25°	307.0
27.5°	215.8
30°	155.3
32.5°	111.5
35°	79.1
37.5°	55.2
40°	39.6
42.5°	28.8
45°	21.6
47.5°	16.8
50°	11.4
52.5°	7.2
55°	5.4
57.5°	4.2
60°	3.0
62.5°	2.4
65°	1.8



TEST NUMBER: P761052

CATALOG NUMBER: LD6D15D010-EU6DR2015309030-6LBSQW1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.2
70°		0.6

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)