

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763637

Luminaire Tested: LD6D25D010-EU6DR6020359050-6LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P763637  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D25D010-EU6DR6020359050-6LBSQW1B  
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2432.6 lumens  
Efficiency: N/A  
Efficacy: 96.9 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.84  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P763637

CATALOG NUMBER: LD6D25D010-EU6DR6020359050-6LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P763637

CATALOG NUMBER: LD6D25D010-EU6DR6020359050-6LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93															
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86															
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80				80															
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75				75															
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70															
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66				66															
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62				62															
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59				59															
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55															
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53				53															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	315654
5°	323430
10°	327336
15°	311824
20°	274939
25°	222377
30°	150425
35°	75375
40°	12223
45°	11975
50°	12205
55°	12382
60°	12740
65°	13030
70°	13321
75°	13509
80°	13025
85°	10907

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 13509 cd/sqm



TEST NUMBER: P763637

CATALOG NUMBER: LD6D25D010-EU6DR6020359050-6LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	281.8	11.6
10°-20°	762.5	31.3
20°-30°	820.4	33.7
30°-40°	356.6	14.7
40°-50°	59.9	2.5
50°-60°	58.2	2.4
60°-70°	49.8	2.0
70°-80°	33.3	1.4
80°-90°	10.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1864.8	76.7
0°-40°	2221.4	91.3
0°-60°	2339.5	96.2
0°-90°	2432.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2432.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2889	
5°	2949	282
15°	2757	763
25°	1845	820
35°	565	357
45°	78	60
55°	65	58
65°	50	50
75°	32	33
85°	9	10
90°	0	



TEST NUMBER: P763637

CATALOG NUMBER: LD6D25D010-EU6DR6020359050-6LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2889.0
2.5°	2970.3
5°	2948.9
7.5°	2955.6
10°	2950.4
12.5°	2889.4
15°	2756.7
17.5°	2578.5
20°	2364.6
22.5°	2135.6
25°	1844.6
27.5°	1475.3
30°	1192.3
32.5°	918.9
35°	565.1
37.5°	241.8
40°	85.7
42.5°	79.0
45°	77.5
47.5°	74.8
50°	71.8
52.5°	68.4
55°	65.0
57.5°	61.6
60°	58.3
62.5°	54.5
65°	50.4
67.5°	46.2
70°	41.7
72.5°	36.8
75°	32.0
77.5°	26.3
80°	20.7
82.5°	14.7
85°	8.7
87.5°	3.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)