

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761682

Luminaire Tested: LD6D15D010-EU6DR600215IC9040-6LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P761682  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D15D010-EU6DR600215IC9040-6LBSQW1B  
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1212.4 lumens  
Efficiency: N/A  
Efficacy: 76.7 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P761682  
CATALOG NUMBER: LD6D15D010-EU6DR600215IC9040-6LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P761682

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9040-6LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	157325
5°	161194
10°	163147
15°	155409
20°	137028
25°	110839
30°	74966
35°	37574
40°	6090
45°	5964
50°	6085
55°	6172
60°	6337
65°	6489
70°	6645
75°	6712
80°	6481
85°	5391

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 6712 cd/sqm



TEST NUMBER: P761682

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9040-6LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.5	11.6
10°-20°	380.0	31.3
20°-30°	408.9	33.7
30°-40°	177.7	14.7
40°-50°	29.9	2.5
50°-60°	29.0	2.4
60°-70°	24.8	2.0
70°-80°	16.6	1.4
80°-90°	5.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	929.4	76.7
0°-40°	1107.2	91.3
0°-60°	1166.0	96.2
0°-90°	1212.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1212.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1440	
5°	1470	140
15°	1374	380
25°	919	409
35°	282	178
45°	39	30
55°	32	29
65°	25	25
75°	16	17
85°	4	5
90°	0	



TEST NUMBER: P761682

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9040-6LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1439.9
2.5°	1480.4
5°	1469.7
7.5°	1473.1
10°	1470.5
12.5°	1440.1
15°	1373.9
17.5°	1285.1
20°	1178.5
22.5°	1064.4
25°	919.4
27.5°	735.3
30°	594.2
32.5°	458.0
35°	281.7
37.5°	120.5
40°	42.7
42.5°	39.4
45°	38.6
47.5°	37.3
50°	35.8
52.5°	34.1
55°	32.4
57.5°	30.7
60°	29.0
62.5°	27.2
65°	25.1
67.5°	23.0
70°	20.8
72.5°	18.4
75°	15.9
77.5°	13.1
80°	10.3
82.5°	7.3
85°	4.3
87.5°	1.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)