

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761683

Luminaire Tested: LD6D15D010-EU6DR600215IC9040-6LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P761683  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D15D010-EU6DR600215IC9040-6LBSQW1MW  
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1365.8 lumens  
Efficiency: N/A  
Efficacy: 86.4 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P761683

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9040-6LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P761683

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9040-6LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	177221
5°	181583
10°	183783
15°	175068
20°	154352
25°	124848
30°	84454
35°	42309
40°	6860
45°	6722
50°	6850
55°	6953
60°	7146
65°	7316
70°	7475
75°	7557
80°	7299
85°	6143

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 7557 cd/sqm



TEST NUMBER: P761683

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9040-6LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.2	11.6
10°-20°	428.1	31.3
20°-30°	460.6	33.7
30°-40°	200.2	14.7
40°-50°	33.6	2.5
50°-60°	32.7	2.4
60°-70°	28.0	2.0
70°-80°	18.7	1.4
80°-90°	5.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1047.0	76.7
0°-40°	1247.2	91.3
0°-60°	1313.5	96.2
0°-90°	1365.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1365.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1622	
5°	1656	158
15°	1548	428
25°	1036	461
35°	317	200
45°	44	34
55°	36	33
65°	28	28
75°	18	19
85°	5	6
90°	0	



TEST NUMBER: P761683

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9040-6LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1622.0
2.5°	1667.6
5°	1655.6
7.5°	1659.4
10°	1656.5
12.5°	1622.3
15°	1547.7
17.5°	1447.7
20°	1327.5
22.5°	1199.0
25°	1035.6
27.5°	828.3
30°	669.4
32.5°	515.9
35°	317.2
37.5°	135.7
40°	48.1
42.5°	44.3
45°	43.5
47.5°	42.0
50°	40.3
52.5°	38.4
55°	36.5
57.5°	34.6
60°	32.7
62.5°	30.6
65°	28.3
67.5°	26.0
70°	23.4
72.5°	20.7
75°	17.9
77.5°	14.8
80°	11.6
82.5°	8.3
85°	4.9
87.5°	1.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)