

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763861

Luminaire Tested: LD6D30D010-EU6DR1515309050-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P763861
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D30D010-EU6DR1515309050-6LBCSSQMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3159.7 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763861

CATALOG NUMBER: LD6D30D010-EU6DR1515309050-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P763861

CATALOG NUMBER: LD6D30D010-EU6DR1515309050-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4843984	4843984	4843984
5°	2846554	2809694	2831920
10°	849566	855519	868610
15°	211323	215440	208786
20°	63224	73215	64566
25°	22287	28395	22576
30°	8185	10783	8327
35°	4103	4633	3972
40°	2585	2848	2585
45°	1911	2044	1911
50°	1523	1523	1523
55°	1267	1267	1267
60°	1025	1025	1025
65°	778	778	778
70°	666	666	666
75°	416	416	552
80°	284	284	284
85°	149	149	149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 2044 cd/sqm



TEST NUMBER: P763861

CATALOG NUMBER: LD6D30D010-EU6DR1515309050-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2049.3	64.9
10°-20°	842.9	26.7
20°-30°	167.4	5.3
30°-40°	41.8	1.3
40°-50°	22.0	0.7
50°-60°	16.3	0.5
60°-70°	11.5	0.4
70°-80°	6.6	0.2
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3059.6	96.8
0°-40°	3101.4	98.2
0°-60°	3139.6	99.4
0°-90°	3159.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3159.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	43050	43050	43050	43050	43050	
5°	28009	27721	27647	27838	27865	2045
15°	2433	2478	2480	2437	2404	834
25°	286	324	364	323	290	150
35°	56	60	64	60	55	38
45°	27	27	29	27	27	21
55°	18	18	18	18	18	16
65°	11	11	11	11	11	11
75°	6	6	6	6	7	7
85°	2	2	2	2	2	2
90°	0	0	0	0	0	



TEST NUMBER: P763861

CATALOG NUMBER: LD6D30D010-EU6DR1515309050-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	43050.0	43050.0	43050.0	43050.0	43050.0
2.5°	38832.9	38865.7	38878.4	38916.7	39058.8
5°	28009.3	27721.4	27646.6	27838.0	27865.3
7.5°	16591.6	16649.9	16863.2	16910.6	16739.2
10°	9105.0	9179.7	9168.8	9234.4	9309.1
12.5°	4656.4	4598.1	4579.8	4654.5	4550.7
15°	2433.0	2478.5	2480.4	2436.6	2403.8
17.5°	1308.5	1361.4	1448.9	1377.8	1268.4
20°	772.7	820.1	894.8	836.5	789.1
22.5°	477.5	515.8	568.6	523.0	484.8
25°	286.1	324.4	364.5	322.6	289.8
27.5°	169.5	202.3	227.8	200.5	167.7
30°	109.3	127.6	144.0	125.7	111.2
32.5°	76.5	83.8	91.1	83.8	76.5
35°	56.5	60.1	63.8	60.1	54.7
37.5°	43.7	47.4	49.2	45.6	41.9
40°	36.4	38.3	40.1	38.3	36.4
42.5°	31.0	32.8	32.8	32.8	31.0
45°	27.3	27.3	29.2	27.3	27.3
47.5°	23.7	23.7	25.5	23.7	23.7
50°	21.9	21.9	21.9	21.9	21.9
52.5°	20.0	20.0	20.0	20.0	20.0
55°	18.2	18.2	18.2	18.2	18.2
57.5°	16.4	16.4	16.4	16.4	16.4
60°	14.6	14.6	14.6	14.6	14.6
62.5°	12.8	12.8	12.8	12.8	12.8
65°	10.9	10.9	10.9	10.9	10.9
67.5°	10.9	10.9	10.9	10.9	10.9
70°	9.1	9.1	9.1	9.1	9.1
72.5°	7.3	7.3	7.3	7.3	7.3
75°	5.5	5.5	5.5	5.5	7.3
77.5°	5.5	5.5	5.5	5.5	5.5
80°	3.6	3.6	3.6	3.6	3.6
82.5°	3.6	3.6	3.6	3.6	3.6
85°	1.8	1.8	1.8	1.8	1.8
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)