

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761769

Luminaire Tested: LD6D15D010-EU6DR650215IC9050-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P761769
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9050-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1004.0 lumens
Efficiency: N/A
Efficacy: 63.5 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761769
CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P761769
 CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93				
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87				
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80				
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75				
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69				
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65				
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60				
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57				
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53				
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108004
5°	108088
10°	111900
15°	112086
20°	103181
25°	87921
30°	67308
35°	47551
40°	28070
45°	11388
50°	4131
55°	2305
60°	1311
65°	724
70°	767
75°	591
80°	629
85°	501

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11388 cd/sqm



TEST NUMBER: P761769

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	9.5
10°-20°	274.6	27.3
20°-30°	329.4	32.8
30°-40°	221.4	22.1
40°-50°	66.3	6.6
50°-60°	11.7	1.2
60°-70°	3.3	0.3
70°-80°	1.6	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.2	69.6
0°-40°	920.5	91.7
0°-60°	998.5	99.5
0°-90°	1004.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1004.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	988	
5°	986	95
15°	991	275
25°	729	329
35°	356	221
45°	74	66
55°	12	12
65°	3	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P761769

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	988.5
2.5°	992.7
5°	985.5
7.5°	1000.4
10°	1008.6
12.5°	1006.6
15°	990.9
17.5°	952.4
20°	887.4
22.5°	811.1
25°	729.3
27.5°	637.0
30°	533.5
32.5°	439.7
35°	356.5
37.5°	274.3
40°	196.8
42.5°	128.5
45°	73.7
47.5°	39.1
50°	24.3
52.5°	16.8
55°	12.1
57.5°	8.7
60°	6.0
62.5°	4.0
65°	2.8
67.5°	2.5
70°	2.4
72.5°	1.8
75°	1.4
77.5°	1.3
80°	1.0
82.5°	0.7
85°	0.4
87.5°	0.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)