

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762003

Luminaire Tested: LD6D20D010-EU6DR2015309024-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P762003
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D20D010-EU6DR2015309024-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1657.0 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P762003
CATALOG NUMBER: LD6D20D010-EU6DR2015309024-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P762003

CATALOG NUMBER: LD6D20D010-EU6DR2015309024-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																
	1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	96	95	94	94	93	92	91	91	90																
	2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	93	92	91	91	90	89	88	88	87																
	3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	90	89	88	88	87	86	85	85	84																
	4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	87	86	85	85	84	83	83	82	81																
	5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	84	83	82	81	81	80	79	79	78																
	6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	82	81	80	80	79	78	78	77	77																
	7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	80	79	78	78	77	76	76	75	75																
	8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	78	77	77	76	75	75	74	74	73																
	9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	76	75	75	74	73	73	72	72	71																
	10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	74	73	73	72	71	71	70	70	69																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1030449
5°	929654
10°	521769
15°	265221
20°	112296
25°	51839
30°	27441
35°	14792
40°	7902
45°	4666
50°	2720
55°	1448
60°	918
65°	646
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4666 cd/sqm



TEST NUMBER: P762003

CATALOG NUMBER: LD6D20D010-EU6DR2015309024-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	671.5	40.5
10°-20°	661.2	39.9
20°-30°	216.0	13.0
30°-40°	73.6	4.4
40°-50°	24.7	1.5
50°-60°	7.5	0.5
60°-70°	2.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1548.7	93.5
0°-40°	1622.2	97.9
0°-60°	1654.4	99.8
0°-90°	1657.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1657.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9431	
5°	8476	671
15°	2345	661
25°	430	216
35°	111	74
45°	30	25
55°	8	7
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P762003

CATALOG NUMBER: LD6D20D010-EU6DR2015309024-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9431.1
0.5°	9431.1
1°	9419.3
1.5°	9395.8
2°	9353.0
2.5°	9295.9
3°	9215.2
3.5°	9102.7
4°	8935.6
4.5°	8732.3
5°	8476.2
5.5°	8139.4
6°	7794.3
6.5°	7398.7
7°	7011.6
7.5°	6558.1
8°	6153.3
8.5°	5746.0
9°	5369.7
9.5°	5024.6
10°	4702.9
12.5°	3376.9
15°	2344.7
17.5°	1531.8
20°	965.8
22.5°	625.7
25°	430.0
27.5°	302.3
30°	217.5
32.5°	156.2
35°	110.9
37.5°	77.3
40°	55.4
42.5°	40.3
45°	30.2
47.5°	23.5
50°	16.0
52.5°	10.1
55°	7.6
57.5°	5.9
60°	4.2
62.5°	3.4
65°	2.5



TEST NUMBER: P762003
CATALOG NUMBER: LD6D20D010-EU6DR2015309024-6LBCSSQMW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.7
70°		0.8

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)