

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761869

Luminaire Tested: LD6D20D010-EU6DR1015209027-6LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761869
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D20D010-EU6DR1015209027-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1605.9 lumens
Efficiency: N/A
Efficacy: 69.5 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761869

CATALOG NUMBER: LD6D20D010-EU6DR1015209027-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P761869

CATALOG NUMBER: LD6D20D010-EU6DR1015209027-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98			98																
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	97			97																
3	111	107	104	102	109	106	103	101	103	101	99	101	99	98	99	98	96	95			95																
4	108	104	101	99	107	103	100	98	101	99	97	99	97	96	98	96	95	94			94																
5	106	102	99	96	105	101	98	96	99	97	95	98	96	94	97	95	94	93			93																
6	104	100	96	94	103	99	96	94	98	95	93	97	94	93	96	94	92	91			91																
7	103	98	95	93	102	97	94	92	96	94	92	95	93	92	95	93	91	90			90																
8	101	96	93	91	100	96	93	91	95	92	91	94	92	90	93	92	90	89			89																
9	100	95	92	90	99	94	92	90	94	91	90	93	91	89	93	91	89	88			88																
10	98	94	91	89	98	93	91	89	93	90	88	92	90	88	92	90	88	87			87																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3820401
5°	1811619
10°	371537
15°	102007
20°	41114
25°	22026
30°	13033
35°	8483
40°	5662
45°	3678
50°	2023
55°	1505
60°	874
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3678 cd/sqm



TEST NUMBER: P761869

CATALOG NUMBER: LD6D20D010-EU6DR1015209027-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1141.9	71.1
10°-20°	309.0	19.2
20°-30°	88.5	5.5
30°-40°	40.4	2.5
40°-50°	18.5	1.2
50°-60°	6.2	0.4
60°-70°	1.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1539.4	95.9
0°-40°	1579.8	98.4
0°-60°	1604.4	99.9
0°-90°	1605.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1605.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	34966	
5°	16518	###
15°	902	309
25°	183	88
35°	64	40
45°	24	19
55°	8	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761869

CATALOG NUMBER: LD6D20D010-EU6DR1015209027-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	34965.9
0.5°	34664.0
1°	33889.4
1.5°	32395.7
2°	30723.3
2.5°	28514.6
3°	26059.6
3.5°	23684.0
4°	21121.8
4.5°	18762.1
5°	16517.6
5.5°	14483.7
6°	12545.1
6.5°	10840.9
7°	9236.1
7.5°	7865.5
8°	6650.0
8.5°	5585.3
9°	4663.7
9.5°	3960.6
10°	3348.8
12.5°	1596.9
15°	901.8
17.5°	548.2
20°	353.6
22.5°	246.3
25°	182.7
27.5°	135.1
30°	103.3
32.5°	79.4
35°	63.6
37.5°	47.7
40°	39.7
42.5°	31.8
45°	23.8
47.5°	15.9
50°	11.9
52.5°	7.9
55°	7.9
57.5°	4.0
60°	4.0
62.5°	4.0
65°	0.0



TEST NUMBER: P761869

CATALOG NUMBER: LD6D20D010-EU6DR1015209027-6LBSQW1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.0
70°		0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)