

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767007

Luminaire Tested: LD6D45BD010-EU6DR7040509027-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P767007
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR7040509027-6LBCSSQMMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4725.7 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767007
CATALOG NUMBER: LD6D45BD010-EU6DR7040509027-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P767007

CATALOG NUMBER: LD6D45BD010-EU6DR7040509027-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97	97	95	94	93											
	1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93	93	92	90	94	91	88	85											
	2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	82	79	85	82	79	78											
	3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78	78	75	74	79	76	73	71											
	4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71	71	68	67	74	70	67	65											
	5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	65	62	62	69	65	62	60											
	6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60	60	57	57	65	61	57	56											
	7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56	56	53	53	61	56	53	51											
	8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	49	49	57	53	49	48											
	9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48	48	46	46	54	49	46	44											
	10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44	44	42	42	50	45	42	40											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	407532
5°	406522
10°	405642
15°	405529
20°	401560
25°	377219
30°	336289
35°	268126
40°	178030
45°	106432
50°	55175
55°	29012
60°	10271
65°	181
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 106432 cd/sqm



TEST NUMBER: P767007

CATALOG NUMBER: LD6D45BD010-EU6DR7040509027-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.5	7.5
10°-20°	1010.9	21.4
20°-30°	1426.1	30.2
30°-40°	1231.1	26.1
40°-50°	551.3	11.7
50°-60°	144.3	3.1
60°-70°	9.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2789.5	59.0
0°-40°	4020.7	85.1
0°-60°	4716.3	99.8
0°-90°	4725.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4725.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3730	
5°	3706	352
15°	3585	1011
25°	3129	1426
35°	2010	1231
45°	689	551
55°	152	144
65°	1	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P767007

CATALOG NUMBER: LD6D45BD010-EU6DR7040509027-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3729.9
2.5°	3725.9
5°	3706.5
7.5°	3690.4
10°	3656.2
12.5°	3625.3
15°	3585.1
17.5°	3538.8
20°	3453.6
22.5°	3313.4
25°	3129.0
27.5°	2915.0
30°	2665.5
32.5°	2360.3
35°	2010.2
37.5°	1623.8
40°	1248.2
42.5°	948.4
45°	688.8
47.5°	474.9
50°	324.6
52.5°	224.0
55°	152.3
57.5°	91.9
60°	47.0
62.5°	14.8
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)