

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767018

Luminaire Tested: LD6D45BD010-EU6DR7040509027-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P767018
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR7040509027-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3952.7 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767018

CATALOG NUMBER: LD6D45BD010-EU6DR7040509027-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P767018

CATALOG NUMBER: LD6D45BD010-EU6DR7040509027-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48555
5°	47112
10°	45798
15°	45198
20°	42205
25°	31707
30°	22414
35°	7938
40°	4174
45°	4447
50°	4604
55°	4691
60°	4720
65°	4620
70°	4360
75°	4040
80°	3586
85°	2908

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 47218 cd/sqm



TEST NUMBER: P767018

CATALOG NUMBER: LD6D45BD010-EU6DR7040509027-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	405.2	10.3
10°-20°	1111.3	28.1
20°-30°	1224.0	31.0
30°-40°	467.6	11.8
40°-50°	220.8	5.6
50°-60°	219.5	5.6
60°-70°	175.7	4.4
70°-80°	101.0	2.6
80°-90°	27.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2740.5	69.3
0°-40°	3208.1	81.2
0°-60°	3648.4	92.3
0°-90°	3952.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3952.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4444	
5°	4296	405
15°	3996	1111
25°	2630	1224
35°	595	468
45°	288	221
55°	246	220
65°	179	176
75°	96	101
85°	23	27
90°	0	



TEST NUMBER: P767018

CATALOG NUMBER: LD6D45BD010-EU6DR7040509027-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4444.0
2.5°	4397.5
5°	4295.5
7.5°	4210.4
10°	4128.0
12.5°	4058.4
15°	3995.8
17.5°	3844.5
20°	3629.9
22.5°	3166.9
25°	2630.1
27.5°	2289.5
30°	1776.6
32.5°	1147.6
35°	595.2
37.5°	321.5
40°	292.7
42.5°	290.6
45°	287.8
47.5°	281.4
50°	270.9
52.5°	258.9
55°	246.3
57.5°	232.2
60°	216.0
62.5°	197.7
65°	178.7
67.5°	157.6
70°	136.5
72.5°	115.4
75°	95.7
77.5°	75.3
80°	57.0
82.5°	40.1
85°	23.2
87.5°	9.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)