

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766565

Luminaire Tested: LD6D45BD010-EU6DR4040509035-6LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P766565  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D45BD010-EU6DR4040509035-6LBCSSQMMMS  
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 40° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4877.4 lumens  
Efficiency: N/A  
Efficacy: 126.0 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P766565

CATALOG NUMBER: LD6D45BD010-EU6DR4040509035-6LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P766565

CATALOG NUMBER: LD6D45BD010-EU6DR4040509035-6LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96						96													
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92						92													
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88						88													
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84						84													
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81						81													
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77						77													
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74						74													
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72						72													
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69						69													
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67						67													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1240743
5°	1234712
10°	1167077
15°	992166
20°	676231
25°	282149
30°	88718
35°	41229
40°	22807
45°	10461
50°	5082
55°	2781
60°	1442
65°	517
70°	224
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10461 cd/sqm



TEST NUMBER: P766565  
 CATALOG NUMBER: LD6D45BD010-EU6DR4040509035-6LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1051.2	21.6
10°-20°	2354.9	48.3
20°-30°	1178.8	24.2
30°-40°	216.1	4.4
40°-50°	59.6	1.2
50°-60°	14.0	0.3
60°-70°	2.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4584.9	94.0
0°-40°	4801.0	98.4
0°-60°	4874.6	99.9
0°-90°	4877.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4877.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11356	
5°	11258	###
15°	8771	2355
25°	2340	1179
35°	309	216
45°	68	60
55°	15	14
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P766565

CATALOG NUMBER: LD6D45BD010-EU6DR4040509035-6LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	11355.8
2.5°	11339.2
5°	11257.6
7.5°	10997.6
10°	10519.3
12.5°	9773.6
15°	8771.3
17.5°	7467.7
20°	5815.9
22.5°	3965.0
25°	2340.4
27.5°	1237.2
30°	703.2
32.5°	454.4
35°	309.1
37.5°	220.9
40°	159.9
42.5°	109.5
45°	67.7
47.5°	43.1
50°	29.9
52.5°	21.2
55°	14.6
57.5°	9.3
60°	6.6
62.5°	4.0
65°	2.0
67.5°	1.3
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)