

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761986

Luminaire Tested: LD6D20D010-EU6DR1515309040-6LBSQW1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P761986  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D20D010-EU6DR1515309040-6LBSQW1B  
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1816.1 lumens  
Efficiency: N/A  
Efficacy: 78.6 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct

Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P761986

CATALOG NUMBER: LD6D20D010-EU6DR1515309040-6LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P761986

CATALOG NUMBER: LD6D20D010-EU6DR1515309040-6LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2784171	2784171	2784171
5°	1636114	1614924	1627699
10°	488307	491722	499252
15°	121461	123823	120001
20°	36338	42081	37115
25°	12815	16320	12978
30°	4703	6200	4785
35°	2360	2665	2280
40°	1484	1633	1484
45°	1099	1176	1099
50°	876	876	876
55°	731	731	731
60°	590	590	590
65°	450	450	450
70°	380	380	380
75°	234	234	317
80°	166	166	166
85°	83	83	83

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 1176 cd/sqm



TEST NUMBER: P761986

CATALOG NUMBER: LD6D20D010-EU6DR1515309040-6LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1177.9	64.9
10°-20°	484.5	26.7
20°-30°	96.2	5.3
30°-40°	24.0	1.3
40°-50°	12.6	0.7
50°-60°	9.4	0.5
60°-70°	6.6	0.4
70°-80°	3.7	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1758.6	96.8
0°-40°	1782.6	98.2
0°-60°	1804.6	99.4
0°-90°	1816.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1816.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	24744	24744	24744	24744	24744	
5°	16099	15933	15890	16000	16016	1176
15°	1398	1425	1426	1400	1382	479
25°	164	186	210	185	167	86
35°	32	35	37	35	31	22
45°	16	16	17	16	16	12
55°	10	10	10	10	10	9
65°	6	6	6	6	6	7
75°	3	3	3	3	4	4
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P761986

CATALOG NUMBER: LD6D20D010-EU6DR1515309040-6LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	24743.8	24743.8	24743.8	24743.8	24743.8
2.5°	22319.9	22338.7	22346.1	22368.1	22449.8
5°	16098.9	15933.4	15890.4	16000.4	16016.1
7.5°	9536.3	9569.9	9692.4	9719.6	9621.2
10°	5233.3	5276.2	5269.9	5307.6	5350.6
12.5°	2676.3	2642.8	2632.3	2675.3	2615.6
15°	1398.4	1424.6	1425.6	1400.5	1381.6
17.5°	752.1	782.5	832.8	791.9	729.1
20°	444.1	471.4	514.3	480.8	453.6
22.5°	274.4	296.4	326.8	300.6	278.6
25°	164.5	186.5	209.5	185.4	166.6
27.5°	97.4	116.3	130.9	115.2	96.4
30°	62.8	73.3	82.8	72.3	63.9
32.5°	44.0	48.2	52.4	48.2	44.0
35°	32.5	34.6	36.7	34.6	31.4
37.5°	25.1	27.2	28.3	26.2	24.1
40°	20.9	22.0	23.0	22.0	20.9
42.5°	17.8	18.9	18.9	18.9	17.8
45°	15.7	15.7	16.8	15.7	15.7
47.5°	13.6	13.6	14.7	13.6	13.6
50°	12.6	12.6	12.6	12.6	12.6
52.5°	11.5	11.5	11.5	11.5	11.5
55°	10.5	10.5	10.5	10.5	10.5
57.5°	9.4	9.4	9.4	9.4	9.4
60°	8.4	8.4	8.4	8.4	8.4
62.5°	7.3	7.3	7.3	7.3	7.3
65°	6.3	6.3	6.3	6.3	6.3
67.5°	6.3	6.3	6.3	6.3	6.3
70°	5.2	5.2	5.2	5.2	5.2
72.5°	4.2	4.2	4.2	4.2	4.2
75°	3.1	3.1	3.1	3.1	4.2
77.5°	3.1	3.1	3.1	3.1	3.1
80°	2.1	2.1	2.1	2.1	2.1
82.5°	2.1	2.1	2.1	2.1	2.1
85°	1.0	1.0	1.0	1.0	1.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)