

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762053

Luminaire Tested: LD6D20D010-EU6DR2015309040-6LBCSSQMB

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P762053  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D20D010-EU6DR2015309040-6LBCSSQMB  
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2060.4 lumens  
Efficiency: N/A  
Efficacy: 89.2 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P762053  
CATALOG NUMBER: LD6D20D010-EU6DR2015309040-6LBCSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P762053

CATALOG NUMBER: LD6D20D010-EU6DR2015309040-6LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	96	95	94	94	93	92	91	91																			
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	93	92	91	91	90	89	88	88																			
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	90	89	88	87	86	85	85	84																			
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	87	86	85	84	83	82	81	81	80																			
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	84	83	82	81	80	79	78	77	77																			
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	82	81	80	79	78	77	76	75	75																			
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	80	79	78	77	76	75	74	73	73																			
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77	76	75	74	73	72	71	71																			
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	76	75	74	73	72	71	70	69	69																			
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	74	73	72	71	70	69	68	67	67																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1281355
5°	1156018
10°	648825
15°	329810
20°	139632
25°	64461
30°	34127
35°	18380
40°	9827
45°	5810
50°	3366
55°	1791
60°	1136
65°	801
70°	319
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5810 cd/sqm



TEST NUMBER: P762053

CATALOG NUMBER: LD6D20D010-EU6DR2015309040-6LBCSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	835.0	40.5
10°-20°	822.2	39.9
20°-30°	268.6	13.0
30°-40°	91.4	4.4
40°-50°	30.7	1.5
50°-60°	9.2	0.4
60°-70°	3.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1925.8	93.5
0°-40°	2017.2	97.9
0°-60°	2057.2	99.8
0°-90°	2060.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2060.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11728	
5°	10540	835
15°	2916	822
25°	535	269
35°	138	91
45°	38	31
55°	9	9
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P762053

CATALOG NUMBER: LD6D20D010-EU6DR2015309040-6LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11727.5
0.5°	11727.5
1°	11712.9
1.5°	11683.6
2°	11630.4
2.5°	11559.3
3°	11459.1
3.5°	11319.1
4°	11111.3
4.5°	10858.6
5°	10540.1
5.5°	10121.3
6°	9692.1
6.5°	9200.3
7°	8718.8
7.5°	8154.9
8°	7651.6
8.5°	7145.1
9°	6677.2
9.5°	6248.0
10°	5848.1
12.5°	4199.1
15°	2915.7
17.5°	1904.8
20°	1200.9
22.5°	778.0
25°	534.7
27.5°	375.9
30°	270.5
32.5°	194.2
35°	137.8
37.5°	96.1
40°	68.9
42.5°	50.1
45°	37.6
47.5°	29.2
50°	19.8
52.5°	12.5
55°	9.4
57.5°	7.3
60°	5.2
62.5°	4.2
65°	3.1



TEST NUMBER: P762053  
CATALOG NUMBER: LD6D20D010-EU6DR2015309040-6LBCSSQMB

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		2.1
70°		1.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)