

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766956

Luminaire Tested: LD6D45BD010-EU6DR6540509035-6LBCSSQMW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P766956  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D45BD010-EU6DR6540509035-6LBCSSQMW  
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4442.0 lumens  
Efficiency: N/A  
Efficacy: 114.8 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P766956  
CATALOG NUMBER: LD6D45BD010-EU6DR6540509035-6LBCSSQMW

### Luminous Intensity Polar Plot





TEST NUMBER: P766956

CATALOG NUMBER: LD6D45BD010-EU6DR6540509035-6LBCSSQMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	235554
5°	234959
10°	234758
15°	227520
20°	207128
25°	180501
30°	150126
35°	118954
40°	85855
45°	54240
50°	28276
55°	15029
60°	7896
65°	4339
70°	1827
75°	2008
80°	1379
85°	1206

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 54240 cd/sqm



TEST NUMBER: P766956

CATALOG NUMBER: LD6D45BD010-EU6DR6540509035-6LBCSSQMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	381.4	8.6
10°-20°	1044.4	23.5
20°-30°	1276.7	28.7
30°-40°	1035.8	23.3
40°-50°	516.2	11.6
50°-60°	144.0	3.2
60°-70°	32.7	0.7
70°-80°	8.5	0.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2702.5	60.8
0°-40°	3738.4	84.2
0°-60°	4398.5	99.0
0°-90°	4442.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4442.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4033	
5°	4008	381
15°	3763	1044
25°	2801	1277
35°	1668	1036
45°	657	516
55°	148	144
65°	31	33
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P766956

CATALOG NUMBER: LD6D45BD010-EU6DR6540509035-6LBCSSQMW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4033.2
2.5°	4030.2
5°	4007.7
7.5°	3994.6
10°	3958.5
12.5°	3885.0
15°	3762.9
17.5°	3572.1
20°	3332.6
22.5°	3074.2
25°	2801.0
27.5°	2508.8
30°	2226.1
32.5°	1946.9
35°	1668.4
37.5°	1390.4
40°	1126.1
42.5°	878.3
45°	656.7
47.5°	457.5
50°	311.2
52.5°	214.5
55°	147.6
57.5°	99.6
60°	67.6
62.5°	46.8
65°	31.4
67.5°	16.0
70°	10.7
72.5°	10.1
75°	8.9
77.5°	5.9
80°	4.1
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)