

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766900

Luminaire Tested: LD6D45BD010-EU6DR6040509040-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P766900
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR6040509040-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4150.9 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P766900
CATALOG NUMBER: LD6D45BD010-EU6DR6040509040-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P766900

CATALOG NUMBER: LD6D45BD010-EU6DR6040509040-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	538623
5°	551867
10°	558537
15°	532082
20°	469126
25°	379450
30°	256667
35°	128621
40°	20867
45°	20427
50°	20822
55°	21144
60°	21721
65°	22234
70°	22745
75°	23007
80°	22211
85°	18554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 23007 cd/sqm



TEST NUMBER: P766900

CATALOG NUMBER: LD6D45BD010-EU6DR6040509040-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	480.9	11.6
10°-20°	1301.1	31.3
20°-30°	1399.9	33.7
30°-40°	608.5	14.7
40°-50°	102.2	2.5
50°-60°	99.4	2.4
60°-70°	85.0	2.0
70°-80°	56.9	1.4
80°-90°	17.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3181.9	76.7
0°-40°	3790.4	91.3
0°-60°	3992.0	96.2
0°-90°	4150.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4150.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4930	
5°	5032	481
15°	4704	1301
25°	3148	1400
35°	964	609
45°	132	102
55°	111	99
65°	86	85
75°	54	57
85°	15	17
90°	0	



TEST NUMBER: P766900

CATALOG NUMBER: LD6D45BD010-EU6DR6040509040-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	4929.7
2.5°	5068.3
5°	5031.7
7.5°	5043.2
10°	5034.3
12.5°	4930.3
15°	4703.9
17.5°	4399.8
20°	4034.7
22.5°	3644.0
25°	3147.5
27.5°	2517.4
30°	2034.4
32.5°	1568.0
35°	964.3
37.5°	412.5
40°	146.3
42.5°	134.7
45°	132.2
47.5°	127.7
50°	122.5
52.5°	116.8
55°	111.0
57.5°	105.2
60°	99.4
62.5°	93.0
65°	86.0
67.5°	78.9
70°	71.2
72.5°	62.9
75°	54.5
77.5°	44.9
80°	35.3
82.5°	25.0
85°	14.8
87.5°	5.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)