

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756965

Luminaire Tested: LD6D02D010-EU6DR200210IC9024-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P756965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR200210IC9024-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 313.2 lumens
Efficiency: N/A
Efficacy: 61.4 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P756965

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9024-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P756965

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9024-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95	94																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	93	92	91																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	90	89	88																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	86	85	83																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	84	83	81																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	82	81	79																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	80	79	77																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77	75																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	76	75	73																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	74	73	71																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194757
5°	175704
10°	98620
15°	50133
20°	21220
25°	9801
30°	5185
35°	2801
40°	1498
45°	881
50°	510
55°	267
60°	175
65°	129
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 881 cd/sqm



TEST NUMBER: P756965

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9024-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.9	40.5
10°-20°	125.0	39.9
20°-30°	40.8	13.0
30°-40°	13.9	4.4
40°-50°	4.7	1.5
50°-60°	1.4	0.4
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	292.7	93.5
0°-40°	306.6	97.9
0°-60°	312.7	99.8
0°-90°	313.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	313.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1782	
5°	1602	127
15°	443	125
25°	81	41
35°	21	14
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756965

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9024-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1782.5
0.5°	1782.5
1°	1780.3
1.5°	1775.8
2°	1767.7
2.5°	1756.9
3°	1741.7
3.5°	1720.4
4°	1688.8
4.5°	1650.4
5°	1602.0
5.5°	1538.4
6°	1473.1
6.5°	1398.4
7°	1325.2
7.5°	1239.5
8°	1163.0
8.5°	1086.0
9°	1014.9
9.5°	949.7
10°	888.9
12.5°	638.2
15°	443.2
17.5°	289.5
20°	182.5
22.5°	118.3
25°	81.3
27.5°	57.1
30°	41.1
32.5°	29.5
35°	21.0
37.5°	14.6
40°	10.5
42.5°	7.6
45°	5.7
47.5°	4.4
50°	3.0
52.5°	1.9
55°	1.4
57.5°	1.1
60°	0.8
62.5°	0.6
65°	0.5



TEST NUMBER: P756965
CATALOG NUMBER: LD6D02D010-EU6DR200210IC9024-6LBCSSQMW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.3
70°		0.2

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)