

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767070

Luminaire Tested: LD6D45BD010-EU6DR7040509050-6LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P767070  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D45BD010-EU6DR7040509050-6LBSQW1MW  
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4338.1 lumens  
Efficiency: N/A  
Efficacy: 112.1 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P767070  
CATALOG NUMBER: LD6D45BD010-EU6DR7040509050-6LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P767070

CATALOG NUMBER: LD6D45BD010-EU6DR7040509050-6LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	532908
5°	517066
10°	502653
15°	496066
20°	463219
25°	347997
30°	246006
35°	87139
40°	45813
45°	48797
50°	50535
55°	51490
60°	51811
65°	50698
70°	47855
75°	44326
80°	39388
85°	31967

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 51814 cd/sqm



TEST NUMBER: P767070

CATALOG NUMBER: LD6D45BD010-EU6DR7040509050-6LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	444.7	10.3
10°-20°	1219.7	28.1
20°-30°	1343.4	31.0
30°-40°	513.3	11.8
40°-50°	242.3	5.6
50°-60°	240.9	5.6
60°-70°	192.9	4.4
70°-80°	110.8	2.6
80°-90°	30.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3007.7	69.3
0°-40°	3521.0	81.2
0°-60°	4004.3	92.3
0°-90°	4338.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4338.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4877	
5°	4714	445
15°	4386	1220
25°	2887	1343
35°	653	513
45°	316	242
55°	270	241
65°	196	193
75°	105	111
85°	26	30
90°	0	



TEST NUMBER: P767070

CATALOG NUMBER: LD6D45BD010-EU6DR7040509050-6LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4877.4
2.5°	4826.4
5°	4714.4
7.5°	4621.0
10°	4530.6
12.5°	4454.2
15°	4385.5
17.5°	4219.4
20°	3983.9
22.5°	3475.8
25°	2886.6
27.5°	2512.8
30°	1949.9
32.5°	1259.5
35°	653.3
37.5°	352.9
40°	321.2
42.5°	318.9
45°	315.8
47.5°	308.9
50°	297.3
52.5°	284.2
55°	270.3
57.5°	254.8
60°	237.1
62.5°	217.0
65°	196.1
67.5°	173.0
70°	149.8
72.5°	126.6
75°	105.0
77.5°	82.6
80°	62.6
82.5°	44.0
85°	25.5
87.5°	10.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)