

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757678

Luminaire Tested: LD6D02D010-EU6DR650210IC9027-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P757678
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR650210IC9027-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 308.9 lumens
Efficiency: N/A
Efficacy: 60.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757678

CATALOG NUMBER: LD6D02D010-EU6DR650210IC9027-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P757678

CATALOG NUMBER: LD6D02D010-EU6DR650210IC9027-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 107 | 105 | 111 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 95 | 94 | 93 | | | 93 | | | | | | | | | | | | | | | | |
| 2 | 107 | 102 | 97 | 94 | 105 | 100 | 96 | 92 | 97 | 93 | 90 | 94 | 91 | 88 | 91 | 89 | 87 | 85 | | | 85 | | | | | | | | | | | | | | | | |
| 3 | 101 | 94 | 88 | 84 | 99 | 92 | 87 | 83 | 90 | 86 | 82 | 87 | 84 | 81 | 85 | 82 | 80 | 78 | | | 78 | | | | | | | | | | | | | | | | |
| 4 | 95 | 87 | 81 | 76 | 93 | 86 | 80 | 76 | 84 | 79 | 75 | 82 | 77 | 74 | 80 | 76 | 73 | 72 | | | 72 | | | | | | | | | | | | | | | | |
| 5 | 90 | 81 | 74 | 70 | 88 | 80 | 74 | 69 | 78 | 73 | 69 | 76 | 72 | 68 | 75 | 71 | 68 | 66 | | | 66 | | | | | | | | | | | | | | | | |
| 6 | 85 | 75 | 69 | 64 | 83 | 74 | 68 | 64 | 73 | 67 | 63 | 71 | 67 | 63 | 70 | 66 | 62 | 61 | | | 61 | | | | | | | | | | | | | | | | |
| 7 | 80 | 70 | 64 | 59 | 79 | 69 | 63 | 59 | 68 | 63 | 59 | 67 | 62 | 58 | 66 | 61 | 58 | 56 | | | 56 | | | | | | | | | | | | | | | | |
| 8 | 76 | 66 | 59 | 55 | 75 | 65 | 59 | 55 | 64 | 58 | 54 | 63 | 58 | 54 | 62 | 57 | 54 | 52 | | | 52 | | | | | | | | | | | | | | | | |
| 9 | 72 | 61 | 55 | 51 | 71 | 61 | 55 | 51 | 60 | 54 | 51 | 59 | 54 | 50 | 58 | 54 | 50 | 49 | | | 49 | | | | | | | | | | | | | | | | |
| 10 | 68 | 58 | 52 | 47 | 67 | 57 | 51 | 47 | 57 | 51 | 47 | 56 | 51 | 47 | 55 | 50 | 47 | 46 | | | 46 | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 16382 |
| 5° | 16339 |
| 10° | 16321 |
| 15° | 15823 |
| 20° | 14407 |
| 25° | 12553 |
| 30° | 10440 |
| 35° | 8271 |
| 40° | 5970 |
| 45° | 3775 |
| 50° | 1972 |
| 55° | 1049 |
| 60° | 549 |
| 65° | 304 |
| 70° | 120 |
| 75° | 135 |
| 80° | 101 |
| 85° | 67 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3775 cd/sqm



TEST NUMBER: P757678

CATALOG NUMBER: LD6D02D010-EU6DR650210IC9027-6LBCSSQMB

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 26.5 | 8.6 |
| 10°-20° | 72.6 | 23.5 |
| 20°-30° | 88.8 | 28.7 |
| 30°-40° | 72.0 | 23.3 |
| 40°-50° | 35.9 | 11.6 |
| 50°-60° | 10.0 | 3.2 |
| 60°-70° | 2.3 | 0.7 |
| 70°-80° | 0.6 | 0.2 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 187.9 | 60.8 |
| 0°-40° | 260.0 | 84.2 |
| 0°-60° | 305.9 | 99.0 |
| 0°-90° | 308.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 308.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 280 | |
| 5° | 279 | 27 |
| 15° | 262 | 73 |
| 25° | 195 | 89 |
| 35° | 116 | 72 |
| 45° | 46 | 36 |
| 55° | 10 | 10 |
| 65° | 2 | 2 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P757678

CATALOG NUMBER: LD6D02D010-EU6DR650210IC9027-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 280.5 |
| 2.5° | 280.2 |
| 5° | 278.7 |
| 7.5° | 277.8 |
| 10° | 275.2 |
| 12.5° | 270.1 |
| 15° | 261.7 |
| 17.5° | 248.4 |
| 20° | 231.8 |
| 22.5° | 213.8 |
| 25° | 194.8 |
| 27.5° | 174.5 |
| 30° | 154.8 |
| 32.5° | 135.4 |
| 35° | 116.0 |
| 37.5° | 96.7 |
| 40° | 78.3 |
| 42.5° | 61.1 |
| 45° | 45.7 |
| 47.5° | 31.8 |
| 50° | 21.7 |
| 52.5° | 14.9 |
| 55° | 10.3 |
| 57.5° | 6.9 |
| 60° | 4.7 |
| 62.5° | 3.3 |
| 65° | 2.2 |
| 67.5° | 1.1 |
| 70° | 0.7 |
| 72.5° | 0.7 |
| 75° | 0.6 |
| 77.5° | 0.4 |
| 80° | 0.3 |
| 82.5° | 0.2 |
| 85° | 0.1 |
| 87.5° | 0.1 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)