

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767629

Luminaire Tested: LD6D50D010-EU6DR6040509024-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P767629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D50D010-EU6DR6040509024-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4448.4 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767629

CATALOG NUMBER: LD6D50D010-EU6DR6040509024-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P767629

CATALOG NUMBER: LD6D50D010-EU6DR6040509024-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	577235
5°	591428
10°	598566
15°	570224
20°	502764
25°	406647
30°	275062
35°	137838
40°	22364
45°	21880
50°	22318
55°	22649
60°	23294
65°	23811
70°	24375
75°	24654
80°	23784
85°	19807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 24654 cd/sqm



TEST NUMBER: P767629

CATALOG NUMBER: LD6D50D010-EU6DR6040509024-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	515.4	11.6
10°-20°	1394.4	31.3
20°-30°	1500.2	33.7
30°-40°	652.1	14.7
40°-50°	109.5	2.5
50°-60°	106.5	2.4
60°-70°	91.1	2.0
70°-80°	60.9	1.4
80°-90°	18.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3410.0	76.7
0°-40°	4062.2	91.3
0°-60°	4278.2	96.2
0°-90°	4448.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4448.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5283	
5°	5392	515
15°	5041	1394
25°	3373	1500
35°	1033	652
45°	142	110
55°	119	106
65°	92	91
75°	58	61
85°	16	18
90°	0	



TEST NUMBER: P767629

CATALOG NUMBER: LD6D50D010-EU6DR6040509024-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5283.1
2.5°	5431.6
5°	5392.4
7.5°	5404.8
10°	5395.1
12.5°	5283.8
15°	5041.1
17.5°	4715.2
20°	4324.0
22.5°	3905.2
25°	3373.1
27.5°	2697.9
30°	2180.2
32.5°	1680.4
35°	1033.4
37.5°	442.1
40°	156.8
42.5°	144.4
45°	141.6
47.5°	136.8
50°	131.3
52.5°	125.1
55°	118.9
57.5°	112.8
60°	106.6
62.5°	99.7
65°	92.1
67.5°	84.6
70°	76.3
72.5°	67.4
75°	58.4
77.5°	48.1
80°	37.8
82.5°	26.8
85°	15.8
87.5°	5.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)