

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767696

Luminaire Tested: LD6D50D010-EU6DR6540509024-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P767696
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D50D010-EU6DR6540509024-6LBCSSQMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4342.5 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767696

CATALOG NUMBER: LD6D50D010-EU6DR6540509024-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P767696

CATALOG NUMBER: LD6D50D010-EU6DR6540509024-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	230275
5°	229695
10°	229498
15°	222423
20°	202492
25°	176460
30°	146761
35°	116287
40°	83934
45°	53026
50°	27640
55°	14693
60°	7721
65°	4243
70°	1776
75°	1963
80°	1379
85°	1139

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 53026 cd/sqm



TEST NUMBER: P767696

CATALOG NUMBER: LD6D50D010-EU6DR6540509024-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	372.9	8.6
10°-20°	1021.1	23.5
20°-30°	1248.1	28.7
30°-40°	1012.6	23.3
40°-50°	504.6	11.6
50°-60°	140.7	3.2
60°-70°	32.0	0.7
70°-80°	8.3	0.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2642.0	60.8
0°-40°	3654.6	84.2
0°-60°	4300.0	99.0
0°-90°	4342.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4342.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3943	
5°	3918	373
15°	3679	1021
25°	2738	1248
35°	1631	1013
45°	642	505
55°	144	141
65°	31	32
75°	9	8
85°	2	2
90°	0	



TEST NUMBER: P767696

CATALOG NUMBER: LD6D50D010-EU6DR6540509024-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3942.8
2.5°	3939.9
5°	3917.9
7.5°	3905.2
10°	3869.8
12.5°	3798.0
15°	3678.6
17.5°	3492.1
20°	3258.0
22.5°	3005.4
25°	2738.3
27.5°	2452.6
30°	2176.2
32.5°	1903.3
35°	1631.0
37.5°	1359.3
40°	1100.9
42.5°	858.7
45°	642.0
47.5°	447.3
50°	304.2
52.5°	209.7
55°	144.3
57.5°	97.3
60°	66.1
62.5°	45.8
65°	30.7
67.5°	15.6
70°	10.4
72.5°	9.8
75°	8.7
77.5°	5.8
80°	4.1
82.5°	2.9
85°	1.7
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)