

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767642

Luminaire Tested: LD6D50D010-EU6DR6040509027-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P767642
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D50D010-EU6DR6040509027-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5039.1 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767642
CATALOG NUMBER: LD6D50D010-EU6DR6040509027-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P767642

CATALOG NUMBER: LD6D50D010-EU6DR6040509027-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	653882
5°	669958
10°	678048
15°	645932
20°	569516
25°	460644
30°	311586
35°	156138
40°	25331
45°	24785
50°	25293
55°	25659
60°	26376
65°	26991
70°	27633
75°	27946
80°	26930
85°	22440

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 27946 cd/sqm



TEST NUMBER: P767642

CATALOG NUMBER: LD6D50D010-EU6DR6040509027-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	583.8	11.6
10°-20°	1579.5	31.3
20°-30°	1699.5	33.7
30°-40°	738.7	14.7
40°-50°	124.1	2.5
50°-60°	120.6	2.4
60°-70°	103.2	2.0
70°-80°	69.0	1.4
80°-90°	20.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3862.8	76.7
0°-40°	4601.5	91.3
0°-60°	4846.2	96.2
0°-90°	5039.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5039.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5985	
5°	6108	584
15°	5710	1580
25°	3821	1699
35°	1171	739
45°	160	124
55°	135	121
65°	104	103
75°	66	69
85°	18	21
90°	0	



TEST NUMBER: P767642

CATALOG NUMBER: LD6D50D010-EU6DR6040509027-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5984.6
2.5°	6152.8
5°	6108.4
7.5°	6122.4
10°	6111.5
12.5°	5985.3
15°	5710.4
17.5°	5341.2
20°	4898.1
22.5°	4423.8
25°	3821.0
27.5°	3056.1
30°	2469.7
32.5°	1903.5
35°	1170.6
37.5°	500.8
40°	177.6
42.5°	163.6
45°	160.4
47.5°	155.0
50°	148.8
52.5°	141.7
55°	134.7
57.5°	127.7
60°	120.7
62.5°	112.9
65°	104.4
67.5°	95.8
70°	86.5
72.5°	76.3
75°	66.2
77.5°	54.5
80°	42.8
82.5°	30.4
85°	17.9
87.5°	6.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)