

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767797

Luminaire Tested: LD6D50D010-EU6DR7040509027-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P767797
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D50D010-EU6DR7040509027-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3485.6 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767797

CATALOG NUMBER: LD6D50D010-EU6DR7040509027-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P767797

CATALOG NUMBER: LD6D50D010-EU6DR7040509027-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	428160
5°	415439
10°	403856
15°	398561
20°	372166
25°	279593
30°	197648
35°	70013
40°	36813
45°	39217
50°	40608
55°	41374
60°	41628
65°	40745
70°	38463
75°	35630
80°	31649
85°	25699

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 41628 cd/sqm



TEST NUMBER: P767797

CATALOG NUMBER: LD6D50D010-EU6DR7040509027-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	357.3	10.2
10°-20°	980.0	28.1
20°-30°	1079.3	31.0
30°-40°	412.4	11.8
40°-50°	194.7	5.6
50°-60°	193.6	5.6
60°-70°	155.0	4.4
70°-80°	89.1	2.6
80°-90°	24.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2416.5	69.3
0°-40°	2828.9	81.2
0°-60°	3217.2	92.3
0°-90°	3485.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3485.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3919	
5°	3788	357
15°	3524	980
25°	2319	1079
35°	525	412
45°	254	195
55°	217	194
65°	158	155
75°	84	89
85°	20	24
90°	0	



TEST NUMBER: P767797

CATALOG NUMBER: LD6D50D010-EU6DR7040509027-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	3918.7
2.5°	3877.7
5°	3787.8
7.5°	3712.7
10°	3640.1
12.5°	3578.7
15°	3523.5
17.5°	3390.1
20°	3200.8
22.5°	2792.6
25°	2319.2
27.5°	2018.9
30°	1566.6
32.5°	1011.9
35°	524.9
37.5°	283.5
40°	258.1
42.5°	256.2
45°	253.8
47.5°	248.2
50°	238.9
52.5°	228.3
55°	217.2
57.5°	204.7
60°	190.5
62.5°	174.3
65°	157.6
67.5°	139.0
70°	120.4
72.5°	101.8
75°	84.4
77.5°	66.4
80°	50.3
82.5°	35.4
85°	20.5
87.5°	8.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)