

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757625

Luminaire Tested: LD6D02D010-EU6DR600210IC9030-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P757625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR600210IC9030-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 326.7 lumens
Efficiency: N/A
Efficacy: 64.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757625

CATALOG NUMBER: LD6D02D010-EU6DR600210IC9030-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P757625

CATALOG NUMBER: LD6D02D010-EU6DR600210IC9030-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	92	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	65	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42404
5°	43444
10°	43968
15°	41875
20°	36928
25°	29862
30°	20199
35°	10124
40°	1640
45°	1607
50°	1632
55°	1657
60°	1704
65°	1758
70°	1789
75°	1815
80°	1762
85°	1379

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 77.5°
 Luminance: 1817 cd/sqm



TEST NUMBER: P757625

CATALOG NUMBER: LD6D02D010-EU6DR600210IC9030-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.9	11.6
10°-20°	102.4	31.4
20°-30°	110.2	33.7
30°-40°	47.9	14.7
40°-50°	8.0	2.5
50°-60°	7.8	2.4
60°-70°	6.7	2.0
70°-80°	4.5	1.4
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	250.5	76.7
0°-40°	298.3	91.3
0°-60°	314.2	96.2
0°-90°	326.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	326.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	388	
5°	396	38
15°	370	102
25°	248	110
35°	76	48
45°	10	8
55°	9	8
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P757625

CATALOG NUMBER: LD6D02D010-EU6DR600210IC9030-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	388.1
2.5°	398.9
5°	396.1
7.5°	397.0
10°	396.3
12.5°	388.1
15°	370.2
17.5°	346.3
20°	317.6
22.5°	286.8
25°	247.7
27.5°	198.2
30°	160.1
32.5°	123.4
35°	75.9
37.5°	32.5
40°	11.5
42.5°	10.6
45°	10.4
47.5°	10.0
50°	9.6
52.5°	9.2
55°	8.7
57.5°	8.3
60°	7.8
62.5°	7.3
65°	6.8
67.5°	6.2
70°	5.6
72.5°	4.9
75°	4.3
77.5°	3.6
80°	2.8
82.5°	1.9
85°	1.1
87.5°	0.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)