

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757014

Luminaire Tested: LD6D02D010-EU6DR200210IC9035-6LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P757014
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR200210IC9035-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 350.4 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757014

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P757014

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	98	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	95	95	94															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	92	92	91															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	89	89	88															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	86	86	85															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	84	84	83															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	82	82	81															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	80	80	79															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	78	78	77															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	76	76	75															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	217910
5°	196598
10°	110336
15°	56094
20°	23743
25°	10959
30°	5804
35°	3121
40°	1669
45°	989
50°	578
55°	305
60°	197
65°	129
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 989 cd/sqm



TEST NUMBER: P757014

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.0	40.5
10°-20°	139.8	39.9
20°-30°	45.7	13.0
30°-40°	15.5	4.4
40°-50°	5.2	1.5
50°-60°	1.6	0.4
60°-70°	0.5	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	327.5	93.5
0°-40°	343.0	97.9
0°-60°	349.8	99.8
0°-90°	350.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	350.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1994	
5°	1792	142
15°	496	140
25°	91	46
35°	23	16
45°	6	5
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P757014

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1994.4
0.5°	1994.4
1°	1991.9
1.5°	1987.0
2°	1977.9
2.5°	1965.8
3°	1948.8
3.5°	1925.0
4°	1889.6
4.5°	1846.7
5°	1792.5
5.5°	1721.3
6°	1648.3
6.5°	1564.6
7°	1482.8
7.5°	1386.9
8°	1301.3
8.5°	1215.1
9°	1135.6
9.5°	1062.6
10°	994.5
12.5°	714.1
15°	495.9
17.5°	323.9
20°	204.2
22.5°	132.3
25°	90.9
27.5°	63.9
30°	46.0
32.5°	33.0
35°	23.4
37.5°	16.3
40°	11.7
42.5°	8.5
45°	6.4
47.5°	5.0
50°	3.4
52.5°	2.1
55°	1.6
57.5°	1.2
60°	0.9
62.5°	0.7
65°	0.5



TEST NUMBER: P757014
CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBSQW1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.4
70°		0.2

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)