

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767654

Luminaire Tested: LD6D50D010-EU6DR6040509030-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P767654
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D50D010-EU6DR6040509030-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4608.5 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767654

CATALOG NUMBER: LD6D50D010-EU6DR6040509030-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P767654

CATALOG NUMBER: LD6D50D010-EU6DR6040509030-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	598006
5°	612717
10°	620112
15°	590743
20°	520856
25°	421283
30°	284965
35°	142800
40°	23163
45°	22668
50°	23117
55°	23468
60°	24125
65°	24664
70°	25269
75°	25540
80°	24665
85°	20559

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 25540 cd/sqm



TEST NUMBER: P767654

CATALOG NUMBER: LD6D50D010-EU6DR6040509030-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	533.9	11.6
10°-20°	1444.6	31.3
20°-30°	1554.2	33.7
30°-40°	675.6	14.7
40°-50°	113.5	2.5
50°-60°	110.3	2.4
60°-70°	94.4	2.0
70°-80°	63.1	1.4
80°-90°	18.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3532.7	76.7
0°-40°	4208.3	91.3
0°-60°	4432.1	96.2
0°-90°	4608.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4608.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5473	
5°	5586	534
15°	5222	1445
25°	3494	1554
35°	1071	676
45°	147	113
55°	123	110
65°	95	94
75°	60	63
85°	16	19
90°	0	



TEST NUMBER: P767654

CATALOG NUMBER: LD6D50D010-EU6DR6040509030-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	5473.2
2.5°	5627.1
5°	5586.5
7.5°	5599.3
10°	5589.3
12.5°	5473.9
15°	5222.5
17.5°	4884.9
20°	4479.6
22.5°	4045.8
25°	3494.5
27.5°	2795.0
30°	2258.7
32.5°	1740.8
35°	1070.6
37.5°	458.0
40°	162.4
42.5°	149.6
45°	146.7
47.5°	141.7
50°	136.0
52.5°	129.6
55°	123.2
57.5°	116.8
60°	110.4
62.5°	103.3
65°	95.4
67.5°	87.6
70°	79.1
72.5°	69.8
75°	60.5
77.5°	49.9
80°	39.2
82.5°	27.8
85°	16.4
87.5°	5.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)