

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767722

Luminaire Tested: LD6D50D010-EU6DR6540509030-6LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P767722  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D50D010-EU6DR6540509030-6LBCSSQMMS  
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5067.7 lumens  
Efficiency: N/A  
Efficacy: 107.8 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P767722  
CATALOG NUMBER: LD6D50D010-EU6DR6540509030-6LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P767722

CATALOG NUMBER: LD6D50D010-EU6DR6540509030-6LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	268734
5°	268060
10°	267827
15°	259573
20°	236309
25°	205929
30°	171275
35°	135709
40°	97947
45°	61881
50°	32255
55°	17147
60°	9006
65°	4947
70°	2083
75°	2279
80°	1581
85°	1340

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 61881 cd/sqm



TEST NUMBER: P767722

CATALOG NUMBER: LD6D50D010-EU6DR6540509030-6LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	435.1	8.6
10°-20°	1191.6	23.5
20°-30°	1456.5	28.7
30°-40°	1181.8	23.3
40°-50°	588.9	11.6
50°-60°	164.3	3.2
60°-70°	37.3	0.7
70°-80°	9.7	0.2
80°-90°	2.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3083.2	60.8
0°-40°	4265.0	84.2
0°-60°	5018.2	99.0
0°-90°	5067.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5067.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4601	
5°	4572	435
15°	4293	1192
25°	3196	1457
35°	1903	1182
45°	749	589
55°	168	164
65°	36	37
75°	10	10
85°	2	2
90°	0	



TEST NUMBER: P767722

CATALOG NUMBER: LD6D50D010-EU6DR6540509030-6LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4601.3
2.5°	4597.9
5°	4572.3
7.5°	4557.4
10°	4516.1
12.5°	4432.3
15°	4293.0
17.5°	4075.3
20°	3802.1
22.5°	3507.3
25°	3195.6
27.5°	2862.2
30°	2539.7
32.5°	2221.2
35°	1903.4
37.5°	1586.3
40°	1284.7
42.5°	1002.1
45°	749.2
47.5°	522.0
50°	355.0
52.5°	244.8
55°	168.4
57.5°	113.6
60°	77.1
62.5°	53.4
65°	35.8
67.5°	18.3
70°	12.2
72.5°	11.5
75°	10.1
77.5°	6.8
80°	4.7
82.5°	3.4
85°	2.0
87.5°	1.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)