

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757173

Luminaire Tested: LD6D02D010-EU6DR300210IC9040-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P757173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR300210IC9040-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 350.7 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757173
CATALOG NUMBER: LD6D02D010-EU6DR300210IC9040-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P757173

CATALOG NUMBER: LD6D02D010-EU6DR300210IC9040-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	86318	86318	86318
5°	83836	83743	83843
10°	72618	72105	72602
15°	47380	47126	46888
20°	23557	24445	23524
25°	11866	13386	11621
30°	4746	5179	4145
35°	2205	2112	1766
40°	949	1059	899
45°	671	834	671
50°	226	607	250
55°	133	254	133
60°	92	107	92
65°	54	54	54
70°	45	22	45
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 834 cd/sqm



TEST NUMBER: P757173

CATALOG NUMBER: LD6D02D010-EU6DR300210IC9040-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.2	28.3
10°-20°	159.7	45.5
20°-30°	69.0	19.7
30°-40°	15.7	4.5
40°-50°	5.4	1.5
50°-60°	1.3	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	327.9	93.5
0°-40°	343.6	98.0
0°-60°	350.3	99.9
0°-90°	350.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	350.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1091	1090	1090	1092	1091	99
15°	598	591	595	593	592	160
25°	140	146	158	142	138	67
35°	24	24	23	22	19	16
45°	6	8	8	8	6	4
55°	1	1	2	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P757173

CATALOG NUMBER: LD6D02D010-EU6DR300210IC9040-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1127.7	1127.7	1127.7	1127.7	1127.7
2.5°	1120.2	1119.4	1119.9	1120.4	1120.6
5°	1091.1	1090.1	1089.9	1092.2	1091.2
7.5°	1032.5	1031.0	1028.7	1033.9	1038.7
10°	934.3	932.6	927.7	930.1	934.1
12.5°	789.3	783.9	783.8	791.5	790.5
15°	597.9	590.7	594.7	592.7	591.7
17.5°	402.0	399.3	404.6	403.0	396.1
20°	289.2	290.0	300.1	295.0	288.8
22.5°	211.1	213.7	225.7	212.6	207.8
25°	140.5	145.8	158.5	142.1	137.6
27.5°	86.4	88.9	101.6	85.3	82.9
30°	53.7	52.5	58.6	50.2	46.9
32.5°	35.3	33.7	35.6	32.0	29.2
35°	23.6	24.1	22.6	22.4	18.9
37.5°	14.7	17.0	15.0	15.9	12.2
40°	9.5	12.3	10.6	11.7	9.0
42.5°	7.8	9.5	8.7	9.2	8.0
45°	6.2	7.7	7.7	7.7	6.2
47.5°	3.4	5.2	6.6	5.3	3.7
50°	1.9	2.6	5.1	2.7	2.1
52.5°	1.3	1.5	3.5	1.5	1.4
55°	1.0	1.0	1.9	1.1	1.0
57.5°	0.8	0.8	1.0	0.8	0.8
60°	0.6	0.6	0.7	0.7	0.6
62.5°	0.5	0.5	0.5	0.5	0.5
65°	0.3	0.3	0.3	0.3	0.3
67.5°	0.2	0.2	0.2	0.2	0.2
70°	0.2	0.1	0.1	0.1	0.2
72.5°	0.1	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)