

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757327

Luminaire Tested: LD6D02D010-EU6DR400210IC9040-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P757327
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR400210IC9040-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 387.0 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757327

CATALOG NUMBER: LD6D02D010-EU6DR400210IC9040-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P757327

CATALOG NUMBER: LD6D02D010-EU6DR400210IC9040-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96																																				
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92																																				
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88																																				
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84																																				
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81																																				
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77																																				
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74																																				
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72																																				
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	72	70	69																																				
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98455
5°	97975
10°	92607
15°	78728
20°	53660
25°	22387
30°	7040
35°	3268
40°	1811
45°	834
50°	391
55°	210
60°	109
65°	52
70°	32
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 834 cd/sqm



TEST NUMBER: P757327

CATALOG NUMBER: LD6D02D010-EU6DR400210IC9040-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.4	21.6
10°-20°	186.9	48.3
20°-30°	93.5	24.2
30°-40°	17.1	4.4
40°-50°	4.7	1.2
50°-60°	1.1	0.3
60°-70°	0.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	363.8	94.0
0°-40°	380.9	98.4
0°-60°	386.7	99.9
0°-90°	387.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	387.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	901	
5°	893	83
15°	696	187
25°	186	94
35°	24	17
45°	5	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P757327

CATALOG NUMBER: LD6D02D010-EU6DR400210IC9040-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	901.1
2.5°	899.8
5°	893.3
7.5°	872.7
10°	834.7
12.5°	775.5
15°	696.0
17.5°	592.5
20°	461.5
22.5°	314.6
25°	185.7
27.5°	98.1
30°	55.8
32.5°	36.0
35°	24.5
37.5°	17.5
40°	12.7
42.5°	8.7
45°	5.4
47.5°	3.4
50°	2.3
52.5°	1.7
55°	1.1
57.5°	0.7
60°	0.5
62.5°	0.3
65°	0.2
67.5°	0.1
70°	0.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)