

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757806

Luminaire Tested: LD6D02D010-EU6DR700210IC9040-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P757806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR700210IC9040-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 245.3 lumens
Efficiency: N/A
Efficacy: 48.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757806

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9040-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P757806

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9040-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	68	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	76	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30112
5°	29218
10°	28413
15°	28041
20°	26185
25°	19663
30°	13903
35°	4922
40°	2596
45°	2766
50°	2856
55°	2915
60°	2928
65°	2870
70°	2715
75°	2533
80°	2265
85°	1755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 2928 cd/sqm



TEST NUMBER: P757806

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9040-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.1	10.2
10°-20°	68.9	28.1
20°-30°	75.9	31.0
30°-40°	29.0	11.8
40°-50°	13.7	5.6
50°-60°	13.6	5.5
60°-70°	10.9	4.5
70°-80°	6.3	2.6
80°-90°	1.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	170.0	69.3
0°-40°	199.0	81.1
0°-60°	226.3	92.3
0°-90°	245.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	245.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	276	
5°	266	25
15°	248	69
25°	163	76
35°	37	29
45°	18	14
55°	15	14
65°	11	11
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P757806

CATALOG NUMBER: LD6D02D010-EU6DR700210IC9040-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	275.6
2.5°	272.8
5°	266.4
7.5°	261.2
10°	256.1
12.5°	251.8
15°	247.9
17.5°	238.5
20°	225.2
22.5°	196.4
25°	163.1
27.5°	142.0
30°	110.2
32.5°	71.2
35°	36.9
37.5°	19.9
40°	18.2
42.5°	18.0
45°	17.9
47.5°	17.5
50°	16.8
52.5°	16.0
55°	15.3
57.5°	14.4
60°	13.4
62.5°	12.3
65°	11.1
67.5°	9.8
70°	8.5
72.5°	7.2
75°	6.0
77.5°	4.7
80°	3.6
82.5°	2.5
85°	1.4
87.5°	0.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)