

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767748

Luminaire Tested: LD6D50D010-EU6DR6540509040-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P767748
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D50D010-EU6DR6540509040-6LBCSSQMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5360.5 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767748
CATALOG NUMBER: LD6D50D010-EU6DR6540509040-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P767748

CATALOG NUMBER: LD6D50D010-EU6DR6540509040-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	284263
5°	283543
10°	283305
15°	274568
20°	249963
25°	217825
30°	181168
35°	143551
40°	103604
45°	65457
50°	34118
55°	18135
60°	9520
65°	5238
70°	2203
75°	2415
80°	1682
85°	1407

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 65457 cd/sqm



TEST NUMBER: P767748

CATALOG NUMBER: LD6D50D010-EU6DR6540509040-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	460.3	8.6
10°-20°	1260.4	23.5
20°-30°	1540.7	28.7
30°-40°	1250.1	23.3
40°-50°	622.9	11.6
50°-60°	173.8	3.2
60°-70°	39.5	0.7
70°-80°	10.3	0.2
80°-90°	2.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3261.4	60.8
0°-40°	4511.4	84.2
0°-60°	5308.1	99.0
0°-90°	5360.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5360.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4867	
5°	4836	460
15°	4541	1260
25°	3380	1541
35°	2013	1250
45°	792	623
55°	178	174
65°	38	39
75°	11	10
85°	2	3
90°	0	



TEST NUMBER: P767748

CATALOG NUMBER: LD6D50D010-EU6DR6540509040-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	4867.2
2.5°	4863.6
5°	4836.4
7.5°	4820.7
10°	4777.1
12.5°	4688.4
15°	4541.0
17.5°	4310.7
20°	4021.8
22.5°	3709.9
25°	3380.2
27.5°	3027.6
30°	2686.4
32.5°	2349.6
35°	2013.4
37.5°	1677.9
40°	1358.9
42.5°	1060.0
45°	792.5
47.5°	552.2
50°	375.5
52.5°	258.9
55°	178.1
57.5°	120.2
60°	81.5
62.5°	56.5
65°	37.9
67.5°	19.3
70°	12.9
72.5°	12.2
75°	10.7
77.5°	7.2
80°	5.0
82.5°	3.6
85°	2.1
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)