

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763572

Luminaire Tested: LD6D25D010-EU6DR6020359024-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P763572
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR6020359024-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1979.6 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763572

CATALOG NUMBER: LD6D25D010-EU6DR6020359024-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P763572

CATALOG NUMBER: LD6D25D010-EU6DR6020359024-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	256872
5°	263195
10°	266382
15°	253762
20°	223744
25°	180966
30°	122404
35°	61343
40°	9956
45°	9735
50°	9927
55°	10077
60°	10358
65°	10600
70°	10862
75°	10976
80°	10571
85°	8775

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 10976 cd/sqm



TEST NUMBER: P763572

CATALOG NUMBER: LD6D25D010-EU6DR6020359024-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.4	11.6
10°-20°	620.5	31.3
20°-30°	667.6	33.7
30°-40°	290.2	14.7
40°-50°	48.7	2.5
50°-60°	47.4	2.4
60°-70°	40.5	2.0
70°-80°	27.1	1.4
80°-90°	8.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1517.5	76.7
0°-40°	1807.7	91.3
0°-60°	1903.9	96.2
0°-90°	1979.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1979.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2351	
5°	2400	229
15°	2243	621
25°	1501	668
35°	460	290
45°	63	49
55°	53	47
65°	41	41
75°	26	27
85°	7	8
90°	0	



TEST NUMBER: P763572

CATALOG NUMBER: LD6D25D010-EU6DR6020359024-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2351.0
2.5°	2417.2
5°	2399.7
7.5°	2405.2
10°	2401.0
12.5°	2351.4
15°	2243.4
17.5°	2098.3
20°	1924.3
22.5°	1737.9
25°	1501.1
27.5°	1200.6
30°	970.2
32.5°	747.8
35°	459.9
37.5°	196.8
40°	69.8
42.5°	64.2
45°	63.0
47.5°	60.9
50°	58.4
52.5°	55.7
55°	52.9
57.5°	50.2
60°	47.4
62.5°	44.3
65°	41.0
67.5°	37.6
70°	34.0
72.5°	30.0
75°	26.0
77.5°	21.4
80°	16.8
82.5°	11.9
85°	7.0
87.5°	2.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)