

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763650

Luminaire Tested: LD6D25D010-EU6DR6520359024-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P763650
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR6520359024-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1658.8 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763650

CATALOG NUMBER: LD6D25D010-EU6DR6520359024-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P763650

CATALOG NUMBER: LD6D25D010-EU6DR6520359024-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	178445
5°	178589
10°	184881
15°	185181
20°	170491
25°	145270
30°	111213
35°	78576
40°	46369
45°	18836
50°	6833
55°	3791
60°	2185
65°	1189
70°	1278
75°	971
80°	1007
85°	878

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18836 cd/sqm



TEST NUMBER: P763650

CATALOG NUMBER: LD6D25D010-EU6DR6520359024-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.3	9.5
10°-20°	453.6	27.3
20°-30°	544.3	32.8
30°-40°	365.8	22.1
40°-50°	109.5	6.6
50°-60°	19.3	1.2
60°-70°	5.5	0.3
70°-80°	2.7	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1155.2	69.6
0°-40°	1520.9	91.7
0°-60°	1649.7	99.5
0°-90°	1658.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1658.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1633	
5°	1628	157
15°	1637	454
25°	1205	544
35°	589	366
45°	122	109
55°	20	19
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P763650

CATALOG NUMBER: LD6D25D010-EU6DR6520359024-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1633.2
2.5°	1640.1
5°	1628.3
7.5°	1652.9
10°	1666.4
12.5°	1663.1
15°	1637.1
17.5°	1573.6
20°	1466.3
22.5°	1340.1
25°	1205.0
27.5°	1052.5
30°	881.5
32.5°	726.4
35°	589.1
37.5°	453.3
40°	325.1
42.5°	212.3
45°	121.9
47.5°	64.5
50°	40.2
52.5°	27.8
55°	19.9
57.5°	14.4
60°	10.0
62.5°	6.5
65°	4.6
67.5°	4.2
70°	4.0
72.5°	3.0
75°	2.3
77.5°	2.1
80°	1.6
82.5°	1.1
85°	0.7
87.5°	0.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)