

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768477

Luminaire Tested: LD6D55D010-EU6DR6555659024-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768477
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6555659024-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5001.2 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768477

CATALOG NUMBER: LD6D55D010-EU6DR6555659024-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P768477

CATALOG NUMBER: LD6D55D010-EU6DR6555659024-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91	89	87	85
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58	54	50	49
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	265212
5°	264542
10°	264316
15°	256168
20°	233207
25°	203223
30°	169029
35°	133926
40°	96666
45°	61071
50°	31828
55°	16923
60°	8889
65°	4892
70°	2049
75°	2257
80°	1581
85°	1340

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 61071 cd/sqm



TEST NUMBER: P768477

CATALOG NUMBER: LD6D55D010-EU6DR6555659024-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	429.4	8.6
10°-20°	1175.9	23.5
20°-30°	1437.4	28.7
30°-40°	1166.3	23.3
40°-50°	581.2	11.6
50°-60°	162.1	3.2
60°-70°	36.8	0.7
70°-80°	9.6	0.2
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3042.8	60.8
0°-40°	4209.1	84.2
0°-60°	4952.4	99.0
0°-90°	5001.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5001.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4541	
5°	4512	429
15°	4237	1176
25°	3154	1437
35°	1878	1166
45°	739	581
55°	166	162
65°	35	37
75°	10	10
85°	2	2
90°	0	



TEST NUMBER: P768477

CATALOG NUMBER: LD6D55D010-EU6DR6555659024-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4541.0
2.5°	4537.6
5°	4512.3
7.5°	4497.6
10°	4456.9
12.5°	4374.1
15°	4236.7
17.5°	4021.8
20°	3752.2
22.5°	3461.3
25°	3153.6
27.5°	2824.7
30°	2506.4
32.5°	2192.1
35°	1878.4
37.5°	1565.5
40°	1267.9
42.5°	988.9
45°	739.4
47.5°	515.2
50°	350.3
52.5°	241.6
55°	166.2
57.5°	112.1
60°	76.1
62.5°	52.7
65°	35.4
67.5°	18.0
70°	12.0
72.5°	11.3
75°	10.0
77.5°	6.7
80°	4.7
82.5°	3.3
85°	2.0
87.5°	1.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)