

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768421

Luminaire Tested: LD6D55D010-EU6DR6055659027-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P768421
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6055659027-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5057.6 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768421

CATALOG NUMBER: LD6D55D010-EU6DR6055659027-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P768421

CATALOG NUMBER: LD6D55D010-EU6DR6055659027-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95				93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88				86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82				80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76				75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72				70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67				66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63				62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60				59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57				55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54				53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	656275
5°	672415
10°	680533
15°	648308
20°	571609
25°	462332
30°	312721
35°	156711
40°	25417
45°	24877
50°	25378
55°	25754
60°	26485
65°	27068
70°	27729
75°	28031
80°	27056
85°	22565

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 28031 cd/sqm



TEST NUMBER: P768421

CATALOG NUMBER: LD6D55D010-EU6DR6055659027-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	586.0	11.6
10°-20°	1585.3	31.3
20°-30°	1705.7	33.7
30°-40°	741.4	14.7
40°-50°	124.5	2.5
50°-60°	121.1	2.4
60°-70°	103.5	2.0
70°-80°	69.3	1.4
80°-90°	20.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3877.0	76.7
0°-40°	4618.4	91.3
0°-60°	4864.0	96.2
0°-90°	5057.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5057.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6006	
5°	6131	586
15°	5731	1585
25°	3835	1706
35°	1175	741
45°	161	125
55°	135	121
65°	105	104
75°	66	69
85°	18	21
90°	0	



TEST NUMBER: P768421

CATALOG NUMBER: LD6D55D010-EU6DR6055659027-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6006.5
2.5°	6175.4
5°	6130.8
7.5°	6144.9
10°	6133.9
12.5°	6007.3
15°	5731.4
17.5°	5360.8
20°	4916.1
22.5°	4440.0
25°	3835.0
27.5°	3067.4
30°	2478.7
32.5°	1910.5
35°	1174.9
37.5°	502.6
40°	178.2
42.5°	164.2
45°	161.0
47.5°	155.6
50°	149.3
52.5°	142.3
55°	135.2
57.5°	128.2
60°	121.2
62.5°	113.3
65°	104.7
67.5°	96.1
70°	86.8
72.5°	76.6
75°	66.4
77.5°	54.7
80°	43.0
82.5°	30.5
85°	18.0
87.5°	6.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)