

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768603

Luminaire Tested: LD6D55D010-EU6DR7055659035-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P768603
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR7055659035-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4102.5 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768603
CATALOG NUMBER: LD6D55D010-EU6DR7055659035-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P768603

CATALOG NUMBER: LD6D55D010-EU6DR7055659035-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			53
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			50
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	503954
5°	488978
10°	475349
15°	469111
20°	438058
25°	329094
30°	232633
35°	82404
40°	43331
45°	46155
50°	47798
55°	48689
60°	48993
65°	47958
70°	45267
75°	41920
80°	37249
85°	30212

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 49008 cd/sqm



TEST NUMBER: P768603

CATALOG NUMBER: LD6D55D010-EU6DR7055659035-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	420.5	10.3
10°-20°	1153.5	28.1
20°-30°	1270.4	31.0
30°-40°	485.4	11.8
40°-50°	229.2	5.6
50°-60°	227.8	5.6
60°-70°	182.4	4.4
70°-80°	104.8	2.6
80°-90°	28.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2844.3	69.3
0°-40°	3329.7	81.2
0°-60°	3786.7	92.3
0°-90°	4102.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4102.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4612	
5°	4458	421
15°	4147	1153
25°	2730	1270
35°	618	485
45°	299	229
55°	256	228
65°	186	182
75°	99	105
85°	24	29
90°	0	



TEST NUMBER: P768603

CATALOG NUMBER: LD6D55D010-EU6DR7055659035-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	4612.4
2.5°	4564.2
5°	4458.3
7.5°	4370.0
10°	4284.5
12.5°	4212.2
15°	4147.2
17.5°	3990.2
20°	3767.5
22.5°	3287.0
25°	2729.8
27.5°	2376.3
30°	1843.9
32.5°	1191.1
35°	617.8
37.5°	333.7
40°	303.8
42.5°	301.6
45°	298.7
47.5°	292.1
50°	281.2
52.5°	268.7
55°	255.6
57.5°	241.0
60°	224.2
62.5°	205.2
65°	185.5
67.5°	163.6
70°	141.7
72.5°	119.8
75°	99.3
77.5°	78.1
80°	59.2
82.5°	41.6
85°	24.1
87.5°	9.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)